

1/2" Socket Sets

S106



Manufactured from matt chrome-plated vanadium steel conforming to ISO standards. Supplied in an impact proof, oil and temperature resistant polypropylene transport case.

The S106 set contains:-

- 1/4" hex sockets 4, 4.5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13mm
- 1/4" hex deep sockets 4, 5, 6, 7, 8, 9, 10, 11, 12, 13mm
- 1/2" hex sockets 10, 12, 13, 14, 15, 16, 17, 18, 20, 21, 23, 24, 27, 32, 34mm
- 1/2" hex sockets 3/8, 7/16, 1/2, 9/16, 11/16, 3/4, 13/16, 7/8, 15/16in AF
- 1/2" impact sockets 17, 19, 21, 24mm
- 1/4" socket drivers Phillips No1, 2, 3, 4
- 1/4" socket drivers slotted 4, 5.5, 7mm
- 1/4" socket drivers hex 3, 4, 5, 6, 8, 10mm
- 1/4" socket drivers Pozidriv No 1, 2, 3
- 1/4" socket drivers Torx 8, 10, 15, 20, 25, 27, 30, 40
- 1/4" extension bars 50mm and 100mm
- 1/4" sliding T bar
- 1/4" universal joint 1/4in spinner handle
- 1/2" extension bars 125mm and 250mm
- 1/2" universal joint
- 1/2" spark plug socket 21mm
- 1/2" T-adaptor L-keys Hex 1.5, 2, 2.5mm
- 1/4" ratchet handle
- 1/2in ratchet handle
- Flex head spanners 8-9, 10-11, 12-13, 14-15mm
- Combination spanners 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm

Set	Order Code	Price Per Set
S106	135-6175	

S240 & S240AF



The S240 set contains:-

- Socket dynamic drive 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 27, 30, 32mm
- Extension bar 125mm and 250mm
- Universal joint
- T-adaptor
- Flexible handle 250mm
- Ratchet handle

The S240AF set contains:-

- 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1, 1 1/16, 1 1/8, 1 3/16, 1 1/4 inch AF
- Extension bars 125mm and 250mm
- Universal joint
- T-adaptor
- Spark plug sockets 5/16in and 13/16in AF
- Flexible handle
- Ratchet handle

Set	Order Code	Price Per Set
S240	135-6171	
S240AF	135-6172	

S400





The S400 set contains:-

- Socket dynamic drive 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25, 26, 27, 28, 30, 32mm
- Extension bars 125mm and 250mm
- Universal joint
- T-adaptor
- Flexible handle 250mm
- Ratchet handle
- Combination spanners 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm

Set	Order Code	Price Per Set
S400	135-6175	

S87+7



The S87+7 set contains:-

- 1/4in sockets Dynamic Drive 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13mm
- 1/4in deep sockets Dynamic Drive 4, 5, 6, 7, 8, 9, 10, 11, 13mm
- 1/2in sockets Dynamic Drive 10, 12, 13, 14, 15, 16, 17, 18, 20, 21, 23, 24, 27, 32, 34mm
- 1/2in sockets Dynamic Drive 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16 AF
- 1/2in impact sockets 17, 19, 21, 24mm
- 1/4in socket drivers 1, 2, 3, 4mm
- 1/4in socket drivers slotted 4, 5.5, 7mm
- 1/4in socket drivers Hex 3, 4, 5, 6, 8, 10mm
- 1/4in extension bars 50mm and 100mm
- 1/4in sliding T-bar
- 1/4in universal joint
- 1/4in spinner handle
- 1/2in extension bars 125mm and 250mm
- 1/2in universal joint
- 1/2in spark plug socket 21mm
- 1/2in T-adaptor
- L-keys Hex 1.5, 2, 2.5mm
- 1/4in ratchet handle
- 1/2in ratchet handle
- Flex head spanners 8-9, 10-11, 12-13, 14-15mm
- Combination spanners 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm

Set	Order Code	Price Per Set
S87+7	135-6176	

S910



The S910 set contains:-

- 1/4in sockets Dynamic Drive 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13mm
- 1/4in deep sockets dynamic drive 4, 5, 6, 7, 8, 9, 10, 11, 12, 13mm
- 1/2in sockets dynamic drive 10, 11, 12, 13, 14, 15, 17, 19, 22, 24, 27, 30, 32mm
- 1/4in extension bars 50mm and 100mm
- 1/4in sliding T-bar
- 1/4in universal joint
- 1/4in bit holder
- 1/4in bit adaptor
- 1/4in spinner handle
- 1/4in magnetic adaptor
- 1/4in bits Phillips No.0, 1, 2, 3

- 1/4in magnetic adaptor
- 1/4in bits Phillips No.0, 1,2, 3
- 1/4in bits slotted 4, 5,5, 7mm
- 1/4in bits Pozidriv No. 1, 2, 3
- 1/4in bits Hex 3, 4, 5, 6, 8, 10mm
- 1/4in bits Torx 8, 10, 15, 20, 25, 27, 30, 40
- 3/8in bits Torx 45, 50, 55
- 1/2in extension bars 125mm and 250mm
- 1/2in universal joint
- 1/2in Spark plug socket 21mm
- 1/2 x 3/16in bit holder
- 1/2in T-adaptor
- L-keys hex 1.5, 2, 2.5mm
- 1/4in ratchet handle
- 1/2in ratchet handle
- Flex head wrenches 8-9, 10-11, 12-13, 14-15mm
- Combination wrenches 8, 10, 12, 13, 14, 17mm

488173

Set	Order Code	Price Per Set
S910	135-6177	