



Fuse drawer "Fingergrip" with voltage selector  
(Fuse links not enclosed)

Fuse drawer "Extrasafe" without voltage selector  
(Fuse links not enclosed)



**Description**

- Component:  
Snap-in, Rear Mounting
- 2 Functions:  
Fuseholder for Fuse-links 5 x 20 mm or 6.3 x 32 mm, Voltage selector insert
- Fits to type: **CD**; **CD-Bowdencable**; **KD**; **KD-Bowdencable**; **KEC**; **KFC**
- Approved together with power entry module

**Characteristics**

- Fuse drawer meets requirements of medical standard IEC/EN 60601-1  
The fuse drawer "Fingergrip" can be removed by hand  
For added safety "Extra-Safe" fuse drawers are available  
With spare fuse compartment
- Qualified for use in equipment according IEC/EN 60950

**Other versions on request**

- Fuse drawer with other voltage values

**Weblinks**

Approvals: <http://www.schurter.com/approvals>  
RoHS: <http://www.schurter.com/rohs>

**Voltage Selector Inserts**

Index	Marking on Voltage Selector Insert / Terminal No.					
	yy	KEC KD	1 3	2 4	3 5	4 6
00			-	-	-	-
01			100	120	220	240
02			110	150	220	-
03			110	-	220	-
04			110	220	240	-
05			115	-	230	-
06			117	220	240	-
08			110 V	-	220 V	-
09			220	-	240	-
10			115	220	240	-
11			110	120	220	240
12			115	230	240	-
13			100	110	220	240
14			100	117	220	240
15			100	115	230	-
16			100	120	230	240
17			115	120	230	240
18			115	-	240	-
19			220	120	240	230
20			100	120	230	-
21			100	-	220	-
22			100	120	220	230
23			100	110	120	-
24			200	220	240	-
25			120	-	230	-
27			115	200	230	-
28			-	230	240	-
29			100	117	125	-

Index yy	KEC KD	Marking on Voltage Selector Insert / Terminal No.			
		1 3	2 4	3 5	4 6
30		117	220	240	100
31		117	220	240	100
32		100	110	230	240
34		110	115	230	240
35		100	115	230	240
36		100	110	200	230
37		115	230	240	100
38		110	230	220	240
39		220	230	240	-
40		100	110	208	230
42		100	115	120	230
43		115	-	230	-
44		100	115	208	230
45		100	115	230	230
46		100	120	200	230
48		100	120	208	230

Index "yy" matches the last two characters of the Order Number within the Variants

### Variants

Mounting style	Fuse-Link	Fuseholder	Comment	Order Number
Fingergrip	5 x 20	1 pole	-	4303.2114.yy
Extra-Safe	5 x 20	1 pole	-	4303.2124.yy
Fingergrip	5 x 20	1 pole	-	4303.2406
Extra-Safe	5 x 20	1 pole	-	4303.2408
Fingergrip	5 x 20	1 pole	-	4303.2416
Fingergrip	5 x 20	2-pole	-	4303.2014.yy
Extra-Safe	5 x 20	2-pole	-	4303.2024.yy
Fingergrip	5 x 20	2-pole	-	4303.2401
Extra-Safe	5 x 20	2-pole	-	4303.2403
Fingergrip	5 x 20	2-pole	shorting bar on the neutral side	4303.2036.yy
Extra-Safe	5 x 20	2-pole	shorting bar on the neutral side	4303.2037.yy
Fingergrip	5 x 20	2-pole	shorting bar on the neutral side	4303.2411
Extra-Safe	5 x 20	2-pole	shorting bar on the neutral side	4303.2413
Fingergrip	6.3 x 32	1 pole	-	4303.2614.yy
Extra-Safe	6.3 x 32	1 pole	-	4303.2624.yy
Fingergrip	6.3 x 32	1 pole	-	4303.2906
Extra-Safe	6.3 x 32	1 pole	-	4303.2908
Fingergrip	6.3 x 32	2-pole	-	4303.2514
Extra-Safe	6.3 x 32	2-pole	-	4303.2524.yy
Fingergrip	6.3 x 32	2-pole	-	4303.2714.yy
Extra-Safe	6.3 x 32	2-pole	-	4303.2737.yy
Fingergrip	6.3 x 32	2-pole	-	4303.2901
Extra-Safe	6.3 x 32	2-pole	-	4303.2903
Fingergrip	6.3 x 32	2-pole	shorting bar on the neutral side	4303.2536.yy
Extra-Safe	6.3 x 32	2-pole	shorting bar on the neutral side	4303.2537.yy
Fingergrip	6.3 x 32	2-pole	shorting bar on the neutral side	4303.2911
Extra-Safe	6.3 x 32	2-pole	shorting bar on the neutral side	4303.2913

"yy" see Voltage Selector Inserts Table

**Packaging unit** 50 Pcs