

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0351500390**  
**Status:** **Active**  
**Overview:** VersaBlade Wire-to-Wire Connector System  
**Description:** VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Natural

**Documents:**

<u>Drawing (PDF)</u>	<u>Application Specification 351500000ASKOR-000 (PDF)</u>
<u>3D Model (PDF)</u>	<u>Packaging Specification PK-35150-003-001 (PDF)</u>
<u>3D Model</u>	<u>Datasheet (PDF)</u>
<u>Product Specification PS-35150-001-001 (PDF)</u>	<u>Brochure (PDF)</u>
<u>Application Specification 351500000ASENG-000 (PDF)</u>	<u>RoHS Certificate of Compliance (PDF)</u>

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Accessories
Series	<u>35150</u>
Component Type	Terminal Position Assurance
Overview	<u>VersaBlade Wire-to-Wire Connector System</u>
Product Name	VersaBlade
UPC	800754375481

**Physical**

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-2
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.373/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +120°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	351500000AS_ENG-000, 351500000AS_KOR-000
Packaging Specification	PK-35150-003-001
Product Specification	PS-35150-001-001
Sales Drawing	SD-35150-039X



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

35150 Series

**Use With**

VersaBlade Standard Receptacle Housings  
351500300 , 351500304 , 351500309  
, 351500310 , 351500314 , 351500319  
, 351503319 , 351504319 , 351500600  
, 351500609 , 351500610 , 351500614  
, 351500619 , 351503619 , 351504619  
<br>VersaBlade Standard Plug Housings  
351510310 , 351510314 , 351510319 ,  
351514319 , 351510610 , 351510614 ,  
351510619 , 351513619 <br>VersaBlade  
Multi-Module 2-3-4 Receptacle Housings  
35524 , 2026500909