

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015475100](#)
Status: **Active**
Overview: [SL Modular Connectors](#)
Description: SL FFC/FPC Connector - Single Row Male Version D, 10 Circuits

Documents:

Drawing (PDF)	Product Specification PS-70430-001 (PDF)
3D Model	RoHS Certificate of Compliance (PDF)
3D Model (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	FFC/FPC Connectors
Series	70431
Comments	Male
Overview	SL Modular Connectors
Product Name	SL
UPC	800753603295

Physical

Actuator Type	N/A
Circuits (Loaded)	10
Color - Resin	Black
Contact Position	N/A
Durability (mating cycles max)	50
Flammability	94V-0
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Mounting	N/A
PCB Retention	None
Packaging Type	Tube
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	1.905µm
Polarized to PCB	No
Stackable	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	FFC/FPC

Electrical


Current - Maximum per Contact	2.0A
Voltage - Maximum	250V

Material Info

Engineering Number	A-70431-0254
--------------------	--------------

Reference - Drawing Numbers

Product Specification	PS-70430-001
-----------------------	--------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[70431 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
-------------	-----------

Tool Kit for Standard	622007400
-----------------------	---------------------------

Manual Press FFC	
------------------	--

Standard Manual	622007800
-----------------	---------------------------

Press for FFC	
---------------	--

FFC 2 thru 20 Circuit	638018550
-----------------------	---------------------------

Termination Kit for use in the Molex TM-3000 or TM-4000 press installed into the TM-42 Replacement Crimp Module

This document was generated on 07/07/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION