## **3.81mm Pluggable** Right Angle Header

# multicomp PRO



## Specifications

Current Rating Min. Insulation Withstand Voltage Insulation Resistance Operating Temperature Wire Strip Length Wire Range Screw Torque




: 2,000V AC


: 10 Amperes, 300V AC


: >2,000MΩ 500V DC : -40°C to +105°C

## RoHS Compliant









Dimensions : Millimetres (Inches)

## **Specification Table**

No.	Material		Plating / Finish	Remark
1	Insulating Body	Polyamide 66	-	Green
2	Contact	Phosphor Bronze	Tin Plated	-
3	Cage Clamp	Brass	Ninlatad	-
4	Screw	Steel	Ni plated	-

## **Dimensions Table**

Pitch : 3.81mm (0.15 inch)				
Poles	A (mm)	A (Inch)		
2	8.41	0.331		
3	12.22	0.481		
4	16.03	0.631		
5	19.84	0.781		
6	23.65	0.931		
8	31.27	1.231		
10	38.89	1.531		
12	46.51	1.831		

## Part Number Table

Description	Part Number
Plug 3.81mm Right Angle 10A 02 Way	MC000104
Plug 3.81mm Right Angle 10A 03 Way	MC000105
Plug 3.81mm Right Angle 10A 04 Way	MC000106
Plug 3.81mm Right Angle 10A 05 Way	MC000107
Plug 3.81mm Right Angle 10A 06 Way	MC000108
Plug 3.81mm Right Angle 10A 08 Way	MC000109
Plug 3.81mm Right Angle 10A 10 Way	MC000110
Plug 3.81mm Right Angle 10A 12 Way	MC000111

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

