

## Metric Standard

### Right Hand Cutting



490915

| Size x Pitch<br>(mm) | Type   | Order Code |
|----------------------|--------|------------|
| 2.0 x 0.4            | Taper  | 147-2077   |
| 2.0 x 0.4            | Second | 147-2078   |
| 2.0 x 0.4            | Plug   | 147-2079   |
| 2.5 x 0.45           | Taper  | 147-2080   |
| 2.5 x 0.45           | Second | 147-2081   |
| 2.5 x 0.45           | Plug   | 147-2083   |
| 3.0 x 0.5            | Taper  | 150-6414   |
| 3.0 x 0.5            | Second | 150-6415   |
| 3.0 x 0.5            | Plug   | 150-6416   |
| 3.5 x 0.6            | Taper  | 147-2084   |
| 3.5 x 0.6            | Second | 147-2085   |
| 3.5 x 0.6            | Plug   | 147-2086   |
| 4.0 x 0.7            | Taper  | 147-2087   |
| 4.0 x 0.7            | Second | 147-2088   |
| 4.0 x 0.7            | Plug   | 147-2089   |
| 5.0 x 0.8            | Taper  | 147-2090   |
| 5.0 x 0.8            | Second | 147-2091   |
| 5.0 x 0.8            | Plug   | 147-2092   |
| 6.0 x 1.0            | Taper  | 147-2093   |
| 6.0 x 1.0            | Second | 147-2095   |
| 6.0 x 1.0            | Plug   | 147-1822   |
| 7.0 x 1.0            | Taper  | 147-1823   |
| 7.0 x 1.0            | Second | 147-1824   |
| 7.0 x 1.0            | Plug   | 147-1825   |
| 8.0 x 1.25           | Taper  | 147-1826   |
| 8.0 x 1.25           | Second | 147-1827   |
| 8.0 x 1.25           | Plug   | 147-1828   |
| 9.0 x 1.25           | Taper  | 147-1829   |
| 9.0 x 1.25           | Second | 147-1830   |
| 9.0 x 1.25           | Plug   | 147-1832   |
| 10.0 x 1.5           | Taper  | 147-1833   |
| 10.0 x 1.5           | Second | 147-1834   |
| 10.0 x 1.5           | Plug   | 147-1835   |
| 11.0 x 1.5           | Taper  | 147-1836   |
| 11.0 x 1.5           | Second | 147-1837   |
| 11.0 x 1.5           | Plug   | 147-1838   |
| 12.0 x 1.75          | Taper  | 147-1839   |
| 12.0 x 1.75          | Second | 147-1840   |
| 12.0 x 1.75          | Plug   | 147-1841   |
| 14.0 x 2.0           | Taper  | 147-1842   |
| 14.0 x 2.0           | Second | 147-1844   |
| 14.0 x 2.0           | Plug   | 147-1845   |
| 16.0 x 2.0           | Taper  | 147-1846   |
| 16.0 x 2.0           | Second | 147-1847   |
| 16.0 x 2.0           | Plug   | 147-1848   |
| 18.0 x 2.5           | Taper  | 147-1849   |
| 18.0 x 2.5           | Second | 147-1850   |
| 18.0 x 2.5           | Plug   | 147-1851   |
| 20.0 x 2.5           | Taper  | 147-1852   |
| 20.0 x 2.5           | Second | 147-1853   |
| 20.0 x 2.5           | Plug   | 147-1854   |
| 24.0 x 3.0           | Taper  | 147-1856   |
| 24.0 x 3.0           | Second | 147-1857   |
| 24.0 x 3.0           | Plug   | 147-1858   |
| 27.0 x 3.0           | Taper  | 147-1878   |
| 27.0 x 3.0           | Second | 147-1881   |
| 27.0 x 3.0           | Plug   | 147-1882   |
| 30.0 x 3.5           | Taper  | 147-1883   |
| 30.0 x 3.5           | Second | 147-1884   |
| 30.0 x 3.5           | Plug   | 147-1885   |