


Android devices will require a USB Host Mode (OTG) cable (Tripp Lite U052-06N) to connect the U209-005-DB25 to the device.

USB to Serial Adapter Cable (USB-A to DB25 M/M), 5 ft.

MODEL NUMBER: **U209-005-DB25**



Two connection options in a single cable. Connect devices with a DB9 or DB25 serial port, such as modems, digital cameras, PDAs and ISDN terminals, to the USB Type-A port on your computer or laptop.

Description

If you need to connect a PDA, digital camera, modem or an ISDN terminal with a serial port to your laptop or tablet, then Tripp Lite's U209-005-DB25 USB-to-Serial Cable Adapter is a great choice. The U209-005-DB25 allows you to connect legacy RS232 peripherals with either a 9-pin DB9 or 25-pin DB25 connector to your computer's USB port. The U209-005-DB25 comes with USB A (Male) and DB9 (Male) connectors; the included DB9-to-DB25 cable adapter can be inserted onto the DB9 connector for use in USB-to-DB25 (M/M) connections. The cable is plug-and-play and requires no external power. The U209-005-DB25 supports data transfer rates up to 230 kbps and has a 5 ft. overall length. It is compatible with Windows, Mac and Linux operating systems, as well as Android tablets / phones with a USB Host Mode (OTG) cable (Tripp Lite U052-06N) and OS version 3.2 and above.

Features

- Connect a RS232 serial device to the USB port on your computer
- Connectors: USB-A (M); DB25 (M); DB9 (M)
- No external power is required
- Supports data transfer rates up to 230 kbps
- Premium double-shielded cable with gold-plated contacts, tinned copper braid and an aluminum Mylar foil shield that eliminates cross-talk and reduces EMI/RFI interference
- Compatible with Windows, Mac and Linux computers
- Compatible with Android tablets / phones with USB Host Mode (OTG) support and OS version 3.2 and above

Highlights

- 5 ft. cable length
- No external power is required
- Compatible with Windows, Mac and Linux computers, and Android tablets / phones (See System Requirements)
- Need drivers? Click on the Support Page link on the left

System Requirements

- Compatible with Windows 2000, XP, Server 2003, Vista, 7, Server 2008, 8, 8.1, Server 2012, and 10
- Compatible with Mac OS X 10.6 through 10.12
- Compatible with Linux Redhat 7.3, 8.0 and 9.0 (Linux Kernel 2.4.31 and above; already includes built-in drivers)
- Android devices will require a USB Host Mode (OTG) cable (Tripp Lite's U052-06N) to connect the U209-005-DB25 to the device.

Package Includes

- U209-005-DB25 USB-to-Serial Adapter Cable
- DB9-to-DB25 adapter
- Owner's Manual



Specifications

OVERVIEW	
UPC Code	037332184757
INPUT	
Cable Length (ft.)	5
Cable Length (m)	1.5
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	4.32 x 11.94 x 12.19
Shipping Dimensions (hwd / in.)	1.70 x 4.70 x 4.80
Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	DB9 (MALE)
Side B - Connector 2	DB25 (MALE)
FEATURES & SPECIFICATIONS	
Technology	DB25; Serial (RS232); USB
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>