

## Electronics



## Foamtips™

***The highly absorbent precision cleaning swab with a wide variety of head sizes and shapes***

- Precision cleaning swabs with 100 ppi polyurethane open cell foam head
- Purest medical grade foam
- Foamtips™ Pro swab (CFP50) has a blue scrubber side and a soft absorbent side
- Available in a variety of head sizes and shapes with various handle lengths

### Foamtips™ Pro



Product Number	Package Count	Swab Length	Head Material	Head Width/Length	Handle Material	Handle Thickness
<b>CFP50</b>	50 Swabs	6.75" (17.1 cm)	White Side: 100 ppi Open Cell Foam	White Side: 0.44" x 0.75" (11.1 mm x 19.1 mm)	Polypropylene	0.20" x 0.13" (4.8 mm x 3.3 mm)
			Blue Side: 75 ppi Closed Cell Foam	Blue Side: 0.28" x 0.69" (7.1 mm x 17.5 mm)		

**Foamtips™ #100**

Product Number	Package Count	Swab Length	Head Material	Head Width/Length	Handle Material	Handle Thickness
<b>CF50</b>	50 Swabs	6.10" (15.5 cm)	100 ppi Open Cell Foam	0.38" x 0.88" (9.6 mm x 22.3 mm)	Wood	0.06" x 0.06" (1.5 mm x 1.5 mm)

**Foamtips™ #110**

Product Number	Package Count	Swab Length	Head Material	Head Width/Length	Handle Material	Handle Thickness
<b>CF1050</b>	50 Swabs	5" (12.7 cm)	100 ppi Open Cell Foam	0.82" x 0.38" (20.8 mm x 9.7 mm)	Polypropylene	0.19" x 0.13" (4.8 mm x 3.3 mm)

**Foamtips™ #120**

Product Number	Package Count	Swab Length	Head Material	Head Width/Length	Handle Material	Handle Thickness
<b>CF2050</b>	50 Swabs	5.12" (13.0 cm)	100 ppi Open Cell Foam	0.50" x 1.00" (12.7 mm x 25.4 mm)	Polypropylene	0.19" x 0.05" (4.8 mm x 1.3 mm)

**Foamtips™ #130**

Product Number	Package Count	Swab Length	Head Material	Head Width/Length	Handle Material	Handle Thickness
<b>CF3050</b>	50 Swabs	6.00" (15.4 cm)	100 ppi Open Cell Foam	0.25" x 0.75" (6.3 mm x 19.0 mm)	Polypropylene	0.13" x 0.13" (3.3 mm x 3.3 mm)

**Foamtips™ #140**

Product Number	Package Count	Swab Length	Head Material	Head Width/Length	Handle Material	Handle Thickness
<b>CF4050</b>	50 Swabs	2.87" (7.3 cm)	100 ppi Open Cell Foam	0.19" x 0.50" (4.8 mm x 12.7 mm)	Polypropylene	0.10" x 0.10" (2.7 mm x 2.7 mm)

© Copyright 2006 ITW Chemtronics

[Privacy](#) | [Disclaimer](#) | [Contact Us](#) | [Feedback](#) | [Sitemap](#) | [Admin](#)

Adobe® Reader® is required to open PDF files.

