Note: This datasheet may be out of date.

Please download the latest datasheet of GRM31C5C1H104JA01# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=GRM31C5C1H104JA01%23

"#" indicates a package specification code.

GRM31C5C1H104JA01#
















< List of part numbers with package codes > GRM31C5C1H104JA01L GRM31C5C1H104JA01K



Appearance & Shape







References

Packaging	Specifications	Minimum Order Quantity
L	180Embossed Tape	2000
К	330Embossed Tape	6000

Mass (typ.)		
1 piece	38.0mg	
φ180mm Reel	116g	

1 of 4

Attention

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Note: This datasheet may be out of date.

Please download the latest datasheet of GRM31C5C1H104JA01# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=GRM31C5C1H104JA01%23

"#" indicates a package specification code.

GRM31C5C1H104JA01#



Specifications

Length	3.2±0.2mm
Width	1.6±0.2mm
Thickness	1.6±0.2mm
Capacitance	0.10μF ±5%
Distance between external terminals g	1.5mm min.
External terminal size e	0.3 to 0.8mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	50Vdc
Size code in inch(mm)	1206 (3216M)
тс	0±30ppm/°C
Temperature characteristics (complied standard)	C0G(EIA)
Temperature range of temperature characteristics	25°C to 125°C

2 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Note: This datasheet may be out of date.

Manufacturing Co., Ltd.

"#" indicates a package specification code.


Please download the latest datasheet of GRM31C5C1H104JA01# from the official website of Murata

GRM31C5C1H104JA01#




Characteristic Data


The charts below may show another part number which shares its characteristics.








GRM31C5C1H1O4JAO1 R DCOV, 25degC



GRM31C5C1H104JA01 C-DC bias capchange, 25.0degC, AC1V



GRM31C5C1H1O4JAO1 C-AC Voltage capchange, DCOV, 25.0d

3 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering




Please download the latest datasheet of GRM31C5C1H104JA01# from the official website of Murata Manufacturing Co., Ltd.


http://www.murata.com/en/products/productdetail?partno=GRM31C5C1H104JA01%23

Note: This datasheet may be out of date.

"#" indicates a package specification code.

GRM31C5C1H104JA01#





GRM31C5C1H104JA01 S21 DC0V, 25degC

4 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

