

Kit Contents

multicomp PRO

Newark Order Code: 81AH8532				
Part Number: EC410				
SKU	QTY	Part Number	Brand	Description
42K2831	4	1N4007G	ON SEMICONDUCTOR	STANDARD RECOVERY DIODE, 1 KV, 1 A, SINGLE, 1.35 V, 30 A
58K9570	4	1N4148	ON SEMICONDUCTOR	SMALL SIGNAL DIODE, SINGLE, 100 V, 200 MA, 1 V, 4 NS, 1 A
90R9455	2	1N5231B	MULTICOMP PRO	ZENER SINGLE DIODE, 5.1 V, 500 MW, DO-35, 5 %, 2 PINS, 175 °C
14N9418	4	MCL053PD	MULTICOMP PRO	LED, RED, THROUGH HOLE, T-1 3/4 (5MM), 10 MA, 2.1 V, 650 NM
58K2047	4	PN2222ABU	ON SEMICONDUCTOR	BIPOLAR (BJT) SINGLE TRANSISTOR, NPN, 40 V, 300 MHZ, 625 MW, 1 A, 35 HFE
31Y3455	4	PN2907ATF	ON SEMICONDUCTOR	BIPOLAR (BJT) SINGLE TRANSISTOR, PNP, -60 V, 200 MHZ, 625 MW, -800 MA, 50 HFE
29C5294	2	NTE312	NTE ELECTRONICS	JFET TRANSISTOR, JUNCTION FIELD EFFECT, -30 V, 5 MA, 15 MA, -6 V, TO-92, JFET
58K8772	6	BS170	ON SEMICONDUCTOR	POWER MOSFET, N CHANNEL, 60 V, 500 MA, 1.2 OHM, TO-92, THROUGH HOLE
80AH9065	4	BS250P	DIODES INC.	POWER MOSFET, P CHANNEL, 45 V, 230 MA, 14 OHM, E-LINE, THROUGH HOLE
29AH3548	3	CD4007UBE	TEXAS INSTRUMENTS	IC, COMPLEMENTARY INVERT., 4007
08F9317	4	TL081CP	TEXAS INSTRUMENTS	OPERATIONAL AMPLIFIER, SINGLE, 1 AMPLIFIER, 3 MHZ, 13 V/μS, 7V TO 36V, DIP, 8 PINS
99W1760	1	MCBB830	MULTICOMP	BREADBOARD, SOLDERLESS, ABS (ACRYLONITRILE BUTADIENE STYRENE), 8.5MM, 165MM X 56MM
10R0134	1	WK-2	GLOBAL SPECIALTIES	140 PC. JUMPER WIRE KIT, 22 AWG, SOLID, INSULATED, ASSORTED LENGTHS AND COLORS, PRE-STRIPPED, CASE
03F7071	2	1222	ENERGIZER	BATTERY, 9 V, ALKALINE, 400 MAH, SNAP CONTACT
58K2897	2	2240	KEYSTONE	BATTERY HOLDER, PP3 (9V) X 1, STRAP, WIRE LEADS
10M4287	2	3782-36-2	POMONA	MINIGRABBER® TEST CLIP TO STACKING BANANA PLUG, 36", RED
58K5000	10	MCCFR0W4J0101A50	MULTICOMP PRO	CARBON FILM RESISTOR, 100 OHM, 250MW, 5%
59K8386	10	MCCFR0W4J0511A50	MULTICOMP PRO	CARBON FILM RESISTOR, 510 OHM, 250MW, 5%

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Kit Contents

multicomp PRO

Newark Order Code: 81AH8532				
Part Number: EC410				
SKU	QTY	Part Number	Brand	Description
58K5001	10	MCCFR0W4J0102A50	MULTICOMP PRO	CARBON FILM RESISTOR, 1KOHM, 250MW, 5%
58K5002	10	MCCFR0W4J0103A50	MULTICOMP PRO	CARBON FILM RESISTOR, 10KOHM, 250MW, 5%
58K5003	10	MCCFR0W4J0104A50	MULTICOMP PRO	CARBON FILM RESISTOR, 100KOHM, 250MW 5%
58K5004	10	MCCFR0W4J0105A50	MULTICOMP PRO	CARBON FILM RESISTOR, 1MOHM, 250MW, 5%
58K5025	5	MCCFR0W4J0202A50	MULTICOMP PRO	CARBON FILM RESISTOR, 2KOHM, 250MW, 5%
59K8375	5	MCCFR0W4J0392A50	MULTICOMP PRO	CARBON FILM RESISTOR, 3.9KOHM, 250MW 5%
58K5069	5	MCCFR0W4J0682A50	MULTICOMP PRO	CARBON FILM RESISTOR, 6.8KOHM, 250MW 5%
58K5016	5	MCCFR0W4J0153A50	MULTICOMP PRO	CARBON FILM RESISTOR, 15KOHM, 250MW, 5%
58K5031	5	MCCFR0W4J0223A50	MULTICOMP PRO	CARBON FILM RESISTOR, 22KOHM, 250MW, 5%
58K5044	5	MCCFR0W4J0333A50	MULTICOMP PRO	CARBON FILM RESISTOR, 33KOHM, 250MW, 5%
58K5057	5	MCCFR0W4J0473A50	MULTICOMP PRO	CARBON FILM RESISTOR, 47KOHM, 250MW, 5%
58K5070	5	MCCFR0W4J0683A50	MULTICOMP PRO	CARBON FILM RESISTOR, 68KOHM, 250MW, 5%
58K5017	2	MCCFR0W4J0154A50	MULTICOMP PRO	CARBON FILM RESISTOR, 150KOHM, 250MW 5%
58K5032	2	MCCFR0W4J0224A50	MULTICOMP PRO	CARBON FILM RESISTOR, 220KOHM, 250MW 5%
58K5045	2	MCCFR0W4J0334A50	MULTICOMP PRO	CARBON FILM RESISTOR, 330KOHM, 250MW 5%
58K5058	2	MCCFR0W4J0474A50	MULTICOMP PRO	CARBON FILM RESISTOR, 470KOHM, 250MW 5%
58K5071	2	MCCFR0W4J0684A50	MULTICOMP PRO	CARBON FILM RESISTOR, 680KOHM, 250MW 5%
17M3619	2	3362P-1-103TLF	BOURNS	TRIMPOT, SINGLE TURN, CERMET, TOP ADJUST, 10 KOHM, THROUGH HOLE, 1 TURNS

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO