

Tool case basic set L electric 34-pcs. (44505)



Wiha Werkzeuge GmbH
Obertalstraße 3-7 78136 Schonach
E-Mail: info.de@wiha.com
Tel.: +49 (0)7722 959-0



Article number: 930070401

Order no.: 44505

EAN: 4010995445058

Dimensions: Internal: 42 x 30 x 16 cm / External: 45,7 x 36,7 x 18,3 cm

Application: The basic kit for electricians out on jobs, e.g. ideal for young workers starting their career. Suitable for working in the presence of live parts up to 1,000 V AC.

Material: Polypropylene

In mobile use, it is not easy to carry all the necessary tools while keeping order. With the tool case basic, the mobile electrician has a convincing equipment and does not lose track of things. For the ideal basic equipment, the handy tool case is equipped with a range of high-quality hand tools, of which the majority offer additional safety when working on live parts due to their VDE-certified insulation. In addition, the case offers ample space for further individual additional equipment thanks to extra loops and storage space. The polypropylene case guarantees robustness and can be secured against theft with padlocks at the integrated eyelets (these are not included in the scope of delivery). The ergonomic two-component handle ensures a comfortable carrying experience. The tool case basic is also ideally suited for flights thanks to the air pressure compensation valve and can be clearly assigned to the owner with the existing, self-labelled name plate. Certified to protection class IP 67, the Wiha tool case is dust- and waterproof. With its 20 L capacity and a permissible load-bearing capacity of up to 14.2 kg, it is prepared for a wide range of operating conditions.

Content:

- 1x Professional electric diagonal cutters with DynamicJoint® (43335)
- 1x Stripping pliers Professional electric (26847)
- 1x Crimping pliers Professional electric for wire-end sleeves hex crimping (35861)
- 1x L-key set in Compact holder Hexagonal ball end matt chrome-plated 9-pcs. (01418)
- 1x Stripping tool with self-rotating trailing blade (35969)
- 1x Electrician's Longlife® folding ruler, 2 m metric, 10 segments (42068)
- 1x Electrician's spirit level 40 cm (42074)
- 1x Screwdriver with bit magazine LiftUp electric Phillips, PlusMinus/Pozidriv, slotted with 6 slimBits (38611)
- 1x Screwdriver SoftFinish® electric Slotted 2.5 x 75 mm (00820)

- 1x Screwdriver SoftFinish® electric slimFix Slotted 3.5 x 100 mm (35446)
- 1x Screwdriver SoftFinish® electric slimFix Slotted 5.5 x 125 mm (35391)
- 1x Screwdriver SoftFinish® electric slimFix Slotted 6.5 x 150 mm (35392)
- 1x Screwdriver SoftFinish® electric slimFix Phillips PH1 x 80 mm (35393)
- 1x Screwdriver SoftFinish® electric slimFix Phillips PH2 x 100 mm (35394)
- 1x Screwdriver SoftFinish® electric slimFix Pozidriv PZ1 x 80 mm (35395)
- 1x Screwdriver SoftFinish® electric slimFix Pozidriv PZ2 x 100 mm (35396)
- 1x Screwdriver SoftFinish® electric slimFix PlusMinus/Pozidriv SL/PZ2 x 100 mm (36330)

Application: The basic kit for electricians out on jobs, e.g. ideal for young workers starting their career.
Suitable for working in the presence of live parts up to 1,000 V AC.

Customs tariff number 82060000
