

(/)

Products

Solutions

Support

Sureshbabu



English K

[Products \(/products\)](/products) / [DRAM \(/products/dram\)](/products/dram) / [LPDRAM \(/products/dram/lpdrum\)](/products/dram/lpdrum) /

[LPDRAM Part Catalog \(/products/dram/lpdrum/part-catalog\)](/products/dram/lpdrum/part-catalog) /

[MT53D1024M32D4DT-046 WT \(/products/dram/lpdrum/part-catalog/mt53d1024m32d4dt-046-wt\)](/products/dram/lpdrum/part-catalog/mt53d1024m32d4dt-046-wt)

MT53D1024M32D4DT-046 WT

[Contact Sales \(/support/sales-network\)](/support/sales-network)

Orderable parts

MT53D1024M32D4DT-046 WT:D

Specs

Chipset Validation	N/A
Cycle Time	0.46ns
Data Rate	DDR4-4266
Density	32Gb
FBGA Code	D9WQG
Op. Temp.	-25C to +85C
Part Status	Production

Data Sheets



RoHS



REACH Statement



Simulation Models



Technical Notes



TN-00-08: Thermal Applications

Product Longevity Program	Products	Solutions
Product Longevity Program Start Date	N/A	
Technology	LPDDR4	
Width	x32	

This document describes considerations in thermal applications for Micron memory devices, including thermal impedance, thermal resistance, junction temperature, operating temperature, memory reliability, reliability modeling, device reliability, and high-temperature electronics.

File Type: PDF

Updated: 2020-03-25

Download (http://www.micron.com/-/media/client/global_note/dram/tn0008_tfr_rev=71bbcae453c14b29)

TN-ED-04: GDDR6 Design Guide

This technical note is designed to help designers implement GDDR6 as an off-the-shelf memory with established packaging, handling and testing. It outlines best practices for signal and power integrity, as well as standard GDDR6 DRAM features, to help system designs achieve the high data rates offered by GDDR6.

File Type: PDF

Updated: 2018-07-30

Download (http://www.micron.com/-/media/client/global_note/dram/tn-ed-04_gdd_rev=99faebbda0584cf8)

[See All \(/search/8654d116c22e%22%5d%2c%20d3e6-4d71-95ce-3\)](#)



[Products \(/products\)](#)

[Solutions \(/solutions\)](#)

[Support \(/support\)](#) [Insight \(/insight\)](#)

[About \(/about\)](#)



[\(https://www.facebook.com/MicronIND/\)](https://www.facebook.com/MicronIND/)


 [\(https://twitter.com/microntech\)](https://twitter.com/microntech)



[\(https://www.linkedin.com/company/3690\)](https://www.linkedin.com/company/3690)



[\(https://www.youtube.com/user/MicronTechnology\)](https://www.youtube.com/user/MicronTechnology)



English

K

[Sales \(/support/sales-network\)](#)

[Support \(/support\)](#)

[Contact \(/forms/contact-us\)](#)



[\(https://www.crucial.com/\)](https://www.crucial.com/)

[Legal \(/legal\)](#)

[Privacy \(/privacy\)](#)

©2020 Micron Technology, Inc. All rights reserved. Information, products, and/or Suppliers (/about-us) are subject to change without notice. All information is provided on an "AS IS" commitment/solution without warranties of any kind. Drawings may not be to scale. Micron, the Micron logo, responsibly/suppliers and all other Micron trademarks are the property of Micron Technology, Inc. All other trademarks are the property of their respective owners.