## **Locking Plug**





## **Specifications:**

Wire Size

Connector Type : Terminal Block
Contact Termination : Free Hanging

 Gender
 : Plug

 No. of Contacts
 : 2

 No. of Rows
 : 1

 Pitch Spacing
 : 5.08mm

 Contact Plating
 : Tin

Contact Material : Phosphor Bronze

Current Rating : 16A

Material : Polyamide 6.6

Operating Temperature : -40°C to +105°C

Terminal Type : Cage Clamp

Voltage Rating : CUL: 300V AC


VDE: 380V AC

: CUL: 24 - 2AWG

VDE: 0.2 - 4mm<sup>2</sup>

## **Locking Plug**





Cage Lamp: Steel Dimensions : Millimetres (Inches)

## **Part Number Table**

Description	Α	Part Number
Plug, Free R/A 5.08mm 2 Way Locking	20.3 (0.8)	MC101 508002
Plug, Free R/A 5.08mm 3 Way Locking	25.4 (1)	MC101 508003
Plug, Free R/A 5.08mm 4 Way Locking	30.5 (1.2)	MC101 508004
Plug, Free R/A 5.08mm 5 Way Locking	35.6 (1.4)	MC101 508005
Plug, Free R/A 5.08mm 6 Way Locking	40.6 (1.6)	MC101 508006
Plug, Free R/A 5.08mm 8 Way Locking	50.8 (2)	MC101 508008
Plug, Free R/A 5.08mm 10 Way Locking	61 (2.4)	MC101 508010
Plug, Free R/A 5.08mm 12 Way Locking	71.1 (2.8)	MC101 508012

Dimensions: Millimetres (Inches)

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

