

Micro HDMI Type D Plug to VGA Receptacle with Audio & Power Adaptor

multicomp PRO

**RoHS
Compliant**




Specifications

Convert From	: Micro HDMI Type D Plug, 19 Pin
Convert To	: VGA, 15 Pin + 3.5mm Jack Audio + Micro USB Receptacle
Cable Length	: 190mm
Colour	: Black

Electronic Tests

Open / Short / Intermittence	: 100%
Hi-Pot	: AC 300V, 0.01S, 1mA
Insulation Resistance	: DC 300V, 0.01S, 10MΩ Min.
Conductive Resistance	: 3Ω Max.
Computer Test	: 1080P @ 60Hz

Diagram



Dimensions : Millimetres

No.	Parameter	Specifications
1	Cable	UL20276 [32AWG(7/0.08TC) * 1P + D(7/0.08TC) + Al - My] * 5 + 32AWG(7/0.08TC) * 4C + D(7/0.08BC) + Al-Foil + B(80/0.12 Al-Mg), PVC Jacket, OD: 4.8±0.2mm
2	Connector - A	Micro HDMI Type D Male, 19 Pin, Gold Plated Shell, Gold Flash Contact
3	Connector - B	VGA + 3.5mm Jack Audio + Micro USB Female, 19 Pin, Nickel Plated Shell, Gold Flash Contact, with IC
4	Inner Mold	LDPE
5	Outer Mold	45P PVC
6	Hood	VGA + 3.5mm Jack Audio + Micro USB Female: ABS
7	Dust Cover	Micro HDMI Male: Transparent

Part Number Table

Description	Part Number
Micro HDMI Type D Plug to VGA Receptacle with Audio & Power Adaptor, 190mm, Black	PS000257

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO