



- Excellent quality professional screwdrivers
- Slot screwdrivers have chrome vanadium steel blades
- Phillips and Pozi screwdrivers have chrome molybdenum
- All blades have non-flake corrosion resistant nickel finish, except torx which has gun metal
- Handles are made from polypropylene moulded directly onto the blade

8 Piece set available containing:

- |             |                     |
|-------------|---------------------|
| Slot, 100 2 | Slot, 125 5         |
| Slot, 150 8 | Pozidriv, No. 0 60  |
| Slot, 75 3  | Pozidriv, No. 0 80  |
| Slot, 100 3 | Pozidriv, No. 2 100 |

5 piece set available containing:

- Torx, TX10, 15, 20, 25, 30

Also in Triton range are ball ended hex drivers and forged nut drivers

TEE190A,401838

	Blade length x tip	Order Code	Price Each
	<b>Slot, Parallel Blade</b>		
	50 x 3	281-177	
	75 x 3	281-189	
	100 x 3	281-207	
	150 x 3	281-220	
	200 x 3	281-244	
	75 x 5	281-190	
	100 x 5	281-219	
	150 x 5	281-232	
	200 x 5	281-256	
	250 x 5	281-268	
		<b>Slot, Flared Tip</b>	
75 x 5		281-098	
100 x 6		281-104	
150 x 6.5		281-116	
200 x 6.5		281-130	
150 x 8		281-128	
200 x 8		281-141	
250 x 9.5		281-165	
200 x 10		281-153	
40 x 6.5		281-270	
40 x 9.5		281-281	
		<b>Pozidriv/Supadriv</b>	
	60 x No.0	281-372	
	80 x No.1	281-384	
	100 x No.2	281-396	
	150 x No.0	281-402	
	150 x No.1	281-414	
	150 x No.2	281-426	
	150 x No.3	609-651	
	250 x No.1	281-438	
	250 x No.2	281-440	
	25 x No.1 Chubby	281-475	
	25 x No.2 Chubby	281-487	
	<b>Phillips</b>		
	60 x No.0	281-293	
	80 x No.1	281-300	
	100 x No.2	281-311	
	150 x No.0	281-323	
	150 x No.1	281-335	
	150 x No.2	281-347	
	150 x No.3	609-675	
	250 x No.1	281-359	
	250 x No.2	281-360	
	25 x No.1 Chubby	281-451	
	25 x No.2 Chubby	281-463	
	<b>Torx</b>		
	70 x T6	281-499	
	70 x T7	281-505	
	70 x T8	281-517	
	70 x T9	281-529	
	80 x T10	281-530	
	80 x T15	281-542	
	90 x T20	281-554	
	90 x T25	281-566	
	110 x T27	724-6456	
	110 x T30	724-6468	
	120 x T40	724-6470	
	<b>Sets</b>		
	5 piece Torx	722-5805	