


# Expression Home XP-4100



## DATASHEET / BROCHURE



Save money, space and time with this 3-in-1 with A4 double-sided printing, individual inks, mobile printing and a large LCD screen.

This stylish and affordable 3-in-1 delivers much more than just the basics from its compact footprint. Its prints are clear, vibrant and cost effective thanks to individual inks and double-sided printing. Printing away from a desktop is made easy with a range of compatible mobile printing apps and a 6.1cm LCD screen.

### Sleek and stylish 3-in-1

This affordable, stylish and compact model efficiently uses your space combining printing, scanning and copying facilities in one unit.

### Easy to use

This printer is designed to be effortless to use with all the essentials and a range of extras for your convenience. It's versatile with Wi-Fi for printing and scanning wirelessly around the home, and Wi-Fi Direct for printing without a wireless network. Share scans with Scan-to-cloud, print without a computer using the 6.1cm LCD screen, and double-sided printing reduces paper usage.

### Efficient & affordable


The 603 ink series provides a low-cost yet reliable printing solution. This four-colour ink set can print an array of documents with defined text and graphics. Each colour is supplied individually, so you only replace the colours you need. This makes individual inks 50% more efficient compared to tri-colour cartridges<sup>1</sup>.

### Unleash smart devices

Print and scan from smart devices using Epson's free iPrint app<sup>2</sup>. Feeling artistic? The Epson Creative Print app can print photos directly from Facebook, create custom greeting cards and stationery, and even turn photos into colouring book templates<sup>2</sup>. Alternatively, Email Print makes it possible to print from almost anywhere in the world by simply emailing files to the printer<sup>2</sup>. You can also take advantage of Apple Airprint<sup>2</sup>.

## KEY FEATURES

- **Stylish 3-in-1 with large screen**  
Save money, space and time
- **Mobile printing**  
Freedom to print from almost anywhere<sup>2</sup>
- **Individual inks**  
Save money by only replacing the colour used
- **Wi-Fi & Wi-Fi Direct**  
Wireless printing with or without a network
- **A4 double-sided printing**  
Automatically print on both sides to reduce paper usage



## PRODUCT SPECIFICATIONS

### TECHNOLOGY

Printing Method	Epson Micro Piezo™ print head
Minimum Droplet Size	3 pl, With Variable-Sized Droplet Technology
Ink Technology	Pigment black and Dye colour Inks
Printing Resolution	5,760 x 1,440 DPI

### PRINT

Printing Speed ISO/IEC 24734	10 pages/min Monochrome, 5 pages/min Colour
Maximum Printing Speed	42 Seconds per 10 x 15 cm photo (Epson Premium Glossy Photo Paper), 33 pages/min Monochrome (plain paper 75 g/m <sup>2</sup> ), 15 pages/min Colour (plain paper 75 g/m <sup>2</sup> )
Colours	Black, Cyan, Yellow, Magenta

For detailed information on printing speeds please visit <http://www.epson.eu/testing>.

### SCAN

Optical Resolution	1,200 DPI x 2,400 DPI (Horizontal x Vertical)
Scanner type	Contact image sensor (CIS)

### PAPER / MEDIA HANDLING

Number of paper trays	1
Paper Formats	A4 (21.0x29.7 cm), A5 (14.8x21.0 cm), A6 (10.5x14.8 cm), B5 (17.6x25.7 cm), C6 (Envelope), DL (Envelope), No. 10 (Envelope), Letter Legal, 9 x 13 cm, 10 x 15 cm, 13 x 18 cm, 13 x 20 cm, 20 x 25 cm, 100 x 148 mm, 16:9
Duplex	Yes (A4, plain paper)
Print Margin	0 mm top, 0 mm right, 0 mm bottom, 0 mm left (Wherever margin is defined. Otherwise 3mm top, left, right, bottom.)
Paper Tray Capacity	100 Sheets Standard, 20 Photo Sheets
Media Handling	Automatic duplex (A4, plain paper), Borderless print

### GENERAL

Energy Use	5 Watt (Ready), 0.3 Watt (Power off), 12 Watt (standalone copying, ISO/IEC 24712 pattern), 0.8 Watt (sleep mode)
Product dimensions	375 x 300 x 170 mm (Width x Depth x Height)
Product weight	4.3 kg
Compatible Operating Systems	Mac OS X 10.6.8 or later, Windows 10 (32/64 bit), Windows 7, Windows 8, Windows 8.1, Windows Vista, Windows XP SP3 or later (32-bit), XP Professional x64 Edition SP2
Included Software	Epson Easy Photo Print, Epson Scan 2
WLAN Security	WEP 64 Bit, WEP 128 Bit, WPA PSK (TKIP), WPA PSK (AES)
Mobile and Cloud printing services	Apple AirPrint, Google Cloud Print, Epson Connect (iPrint App, Creative Print App, Email Print, Remote Print Driver, Scan-to-Cloud)
Colour	Black

### OTHER FEATURES

Panel	Type: Color, Diagonal: 6.1 cm
Features	Red eye removal, Photo Enhance

### OTHER

Warranty	12 months Carry in Optional warranty extension available
----------	---

## LOGISTICS INFORMATION

SKU	C11CG33401
EAN code	8715946665436
Country of Origin	Indonesia
Layer	4 Units
Layer Block	6 Units

For more information please contact:

Home users: 0343 90 37766  
Business users\*: 0871 42 37766  
Republic of Ireland: 01 436 7742  
Or visit us at <https://www.epson.co.uk/contactus>  
\* 10p per minute plus network extras.

Web: [www.epson.co.uk](http://www.epson.co.uk)  
[www.epson.ie](http://www.epson.ie)

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.  
Last extracted: 2020-09-10

## Expression Home XP-4100

### WHAT'S IN THE BOX

- Software (CD)
- Setup guide
- Power cable
- Main unit
- Individual Ink Cartridges
- Warranty document

### INK CARTRIDGE COMPATIBILITY



### INK YIELD DATA

	<b>Starfish 603</b>	<b>Starfish 603XL</b>
●	150 pages*	500 pages*
● ● ●	130 pages*	350 pages*

\* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>

1. Based on testing carried out by BLI in July 2019, compared to equivalent competitor (HP and Canon) printer models, using tri-colour cartridges, according to the manufacturers' websites, July 2018. Weighting for Document and Photo printing applied based on TNS 'Printing Usage & Attitudes Study', June 2013.
2. – Epson iPrint and Epson Creative Print require a wireless connection and the Epson printing apps. Epson Email print, Epson Remote Print Driver and Epson scan-to cloud require an internet connection. For more information, supported languages and devices, please visit [www.epsonconnect.eu](http://www.epsonconnect.eu).
3. AirPrint-enabled printers work with iPhone 4s and later, iPad 2 and later, all models of iPad Air and iPad mini, and iPod touch 5th generation with the latest version of iOS, and Mac with the latest version of OS X.

**EPSON**®