

Ring ratchet open-ended spanner set 13 pcs. switchable, with holder (44661)



wiha 

Tools that work for you

Wiha Werkzeuge GmbH
Obertalstraße 3-7 78136 Schonach
E-Mail: info.de@wiha.com
Tel.: +49 (0)7722 959-0

Article number: 303190

Order no.: 44661

EAN: 4010995446611

Increases your efficiency: Fastening without interruption thanks to a finely toothed ring ratchet.

Increases your flexibility: Variably adjustable right or left rotation through switching lever.

Simplifies your work: With a convenient holder for clearly arranged storage and easy withdrawal.

Increases your efficiency: Improved accessibility in confined spaces thanks to 15° jaw positioning.

Drive: For installation and mounting work.

Eminently suitable for working in confined spaces.

Opening tightly fastened screws requires great force. With the leverage action from Wiha's ring ratchet open-ended spanner, the user can easily open any fastening. The jaw end is also excellently suited for tightening screws and nuts. With 15° jaw positioning, the jaw end is perfect for working in confined spaces. Similarly, when working with the ring ratchet, the user benefits from the fine tooting with 72 teeth, offering a short return angle and highest comfort when working in confined spaces due to the double hex design. The right or left rotation can be variably adjusted by the integrated switching lever. Made of high quality chrome vanadium steel, the ring ratchet open-end spanners are distinguished by their longevity and robustness, not the least thanks to their corrosion-resistant and easy to clean surface. The set includes the 12 most commonly used sizes from 8 to 19 mm, neatly stored in a convenient holder. The holder can be opened with a single hand to remove the appropriate size. The non-slip surface finish ensures a strong grip, even in oily or wet work situations.

Based on DIN 3113

Content:

- 1x Ring ratchet open-end spanner Switchable 8 x 139.5 mm (44641)
- 1x Ring ratchet open-end spanner Switchable 9 x 149 mm (44642)
- 1x Ring ratchet open-end spanner Switchable 10 x 158.5 mm (44644)
- 1x Ring ratchet open-end spanner Switchable 11 x 165 mm (44645)
- 1x Ring ratchet open-end spanner Switchable 12 x 171 mm (44646)
- 1x Ring ratchet open-end spanner Switchable 13 x 177.5 mm (44647)

- 1x Ring ratchet open-end spanner Switchable 14 x 190 mm (44648)
- 1x Ring ratchet open-end spanner Switchable 15 x 199 mm (44789)
- 1x Ring ratchet open-end spanner Switchable 16 x 208 mm (44649)
- 1x Ring ratchet open-end spanner Switchable 17 x 225 mm (44650)
- 1x Ring ratchet open-end spanner Switchable 18 x 236 mm (44651)
- 1x Ring ratchet open-end spanner Switchable 19 x 247.5 mm (44652)
- 1x holder

Customs tariff number

82041100
