CI: Carl Kammerling International Ltd.

PRODUCT SPECIFICATION

Brand Kasp

Product Range Van Lock & Hasp

Catalogue number 500

Date 27/04/2007

Range Description

Van lock, Hasp and fixings

Features

The design of the 500 series van lock and hasp makes it almost impervious to common forms of attack, the shackle-less lock is enclosed withing the walls of the hasp offering virtually no points of effective attack

Padlock:

- Chrome plated hardened steel body extra strength and protection from corrosion
- Shrouded steel shackle maximum protection against hacksaw and cropping attacks
- 6 Pin cylinder extra protection against picking
- Corrosion resistant mechanism reliable in potentially harsh environments

Hasp

- Zinc plated heavy duty steel construction extra strength and protection against corrosion
- Supplied complete fixing bolts for security and convenience

The van lock is supplied boxed with an attention drawing promotional sleeve

2 keys are supplied with each Van lock





	T	+	T =	
Item	Item Description	EAN No	Commodity	Carton
Number			code	Qty
K50073	Van lock, Hasp and fixings	5013969901320	83011000	6

Technical product information	Padlock - Solid hardened steel, Chrome plated				
in contact	Hasp- Heavy gauge steel, Zinc plated				
	Locking mechanism- Pin tumbler cylinder type, 6 pin cylinder, Brass pins – Driver pin 6 is plain, driver pins 1 to 5 are mushroom type. Key differs- 3000 Re-keyable – No Security rating:				
	Item Security rating K50073 13				
	Use environment- Harsh outdoor use				
	Recommended applications- Designed specifically for use on commercial vehicles, the van lock and hasp can also be used for other high security applications.				
Standards compliance	None applicable				
User health and safety information	None applicable				
RoHS/WEEE compliance	This product does not fall within the scope of RoHS or WEEE regulations				
Material safety data	None applicable				
Warranty	KASP Van locks are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not covered				
Country of origin	China				

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K50073	213	45	115	2682	250	130	55	2812

	Shelf box (s	secondary pa	Euro Pallet data Wi x Hi			
Item	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
K50073	265	275	180	17201		

Packaging waste details

	Primary Pa	ckaging	aging			Secondary packaging		
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
K17580D			130	Box & Sleeve			329	Box