

# Safe-IT USB-A to USB Mini-B Antibacterial Cable (M/M), USB 2.0, White, 3-ft. (0.91 m)

## MODEL NUMBER: U030AB-003-WH





USB cable with antibacterial properties connects mobile devices to your computer while helping to protect you from harmful bacteria.

#### Features

#### Durable USB-A to USB Mini-B Cable Transfers Important Data at USB 2.0 Speeds

This USB cable (M/M) connects a digital camera, MP3 player, smartphone or other Mini-B peripheral with a 5-pin port to the USB-A port on your computer or laptop. It transfers data at USB 2.0 speeds up to 480 Mbps for use with low-speed and high-speed devices, including multimedia applications. The cable is also backward compatible with earlier USB generations.

#### Provides Extra Protection Against Certain Bacteria

The molded connectors and PVC jacket are constructed using an antibacterial material that is 99.9% effective in inhibiting Escherichia coli (E. coli) and Staphylococcus aureus (staph). This added protection makes this cable an ideal solution for medical facilities, schools, businesses, restaurants/kitchens and anywhere else that needs extra protection against bacteria.

#### Premium Construction for Superior Performance

Manufactured with twisted 28 AWG data lines and 28 AWG power lines, the U030AB-003-WH also features molded gold-plated connectors and contacts that provide maximum conductivity and minimum data loss to guarantee a clear transmission free of interference. Integral strain relief gives the cable extra flexibility, reduces stress and helps the cable move freely without cracking or breaking loose from the connector.

#### White Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The cable has a white PVC jacket, which is easy to identify quickly in a crowded computer or hub and helps prevent the cable from becoming accidentally disconnected.

### Highlights

- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient data transfers
- Made with antibacterial material proven 99.9% effective in inhibiting E. coli and staph
- Foil and braid shielding protects against EMI/RFI noise that can distort or destroy data
- Gold-plated connectors and contacts for maximum conductivity and minimum data loss
- White jacket permits fast, easy identification in a crowded hub or computer

#### Applications

- Connect a computer or laptop and a USB Mini-B peripheral in a home or office network
- Provide extra protection against bacteria to give cable installers and IT personnel peace of mind during installation

#### **Package Includes**

U030AB-003-WH USB-A to USB Mini-B Antibacterial Cable (M/M), White, 3-ft. (0.91 m)

# Specifications

OVERVIEW	
UPC Code	037332260666
Technology	USB 2.0 (High Speed); USB
PHYSICAL	



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

[	
Color	White
Cable Outer Diameter (OD)	3.8MM
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Wire Gauge (AWG)	28/28
Cable Length (ft.)	6
Cable Length (m)	0.9
Cable Length (in.)	36
Material of Construction	PVC
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	14 to 122 F (-10 to 50 C)
Storage Temperature Range	5 to 140 F (-15 to 60 C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB MINI-B 5-PIN (MALE)
Connector Plating	Gold
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
SPECIAL FEATURES	
Antibacterial	Yes
STANDARDS & COMPLIANCE	
Certifications	RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

https://www.tripplite.com/products/product-certification-agencies