





0.3mm Pitch

SERIES

# 6295

0.3mmピッチ RA SMT 下接点 ワンタッチロック

0.3mmPitch RA SMT Bottom contact One-touch lock



極数 NO. OF POS.	A	B	C	D
17	4.8	4.2	6.7	5.5
19	5.4	4.8	7.3	6.1
21	6.0	5.4	7.9	6.7
23	6.6	6.0	8.5	7.3
25	7.2	6.6	9.1	7.9
27	7.8	7.2	9.7	8.5
29	8.4	7.8	10.3	9.1
31	9.0	8.4	10.9	9.7
33	9.6	9.0	11.5	10.3
35	10.2	9.6	12.1	10.9
37	10.8	10.2	12.7	11.5
39	11.4	10.8	13.3	12.1
41	12.0	11.4	13.9	12.7
43	12.6	12.0	14.5	13.3
45	13.2	12.6	15.1	13.9
47	13.8	13.2	15.7	14.5
49	14.4	13.8	16.3	15.1
51	15.0	14.4	16.9	15.7
53	15.6	15.0	17.5	16.3
55	16.2	15.6	18.1	16.9
57	16.8	16.2	18.7	17.5
59	17.4	16.8	19.3	18.1
61	18.0	17.4	19.9	18.7

生産対応可能極数については、営業部  
にご確認願います。  
Feel free to contact our sales  
department for available num-  
bers of positions.

注文コード ORDERING CODE

04 6295 OXX 000 846+

RoHS 対応品

RoHS Compliant Product

極数 NUMBER OF POSITIONS



金めっき Au plated

0.3mm Pitch

SERIES

# 6295

エンボス梱包品  
Tape and Reel Package



SECT. E-E

極数 NO. OF POS.	A	B	C
17	11.5	—	24.0
19	11.5	—	24.0
21	11.5	—	24.0
23	11.5	—	24.0
25	11.5	—	24.0
27	11.5	—	24.0
29	11.5	—	24.0
31	11.5	—	24.0
33	11.5	—	24.0
35	11.5	—	24.0
37	11.5	—	24.0
39	11.5	—	24.0
41	14.2	28.4	32.0
43	14.2	28.4	32.0
45	14.2	28.4	32.0
47	14.2	28.4	32.0
49	14.2	28.4	32.0
51	14.2	28.4	32.0
53	14.2	28.4	32.0
55	14.2	28.4	32.0
57	14.2	28.4	32.0
59	14.2	28.4	32.0
61	14.2	28.4	32.0

生産対応可能極数については、営業部  
にご確認願います。  
Feel free to contact our sales  
department for available num-  
bers of positions.

注文コード ORDERING CODE

04 6295 0XX 000 846+

極数 NUMBER OF POSITIONS

RoHS 対応品

RoHS Compliant Product

金めっき Au plated

梱包数量 2000個/リール  
PACKING QUANTITY : 2000/Reel