



ELECTRONIC-SERVICE TOOL SETS

Special service sets for the maintenance and repairing of mobile phones and other high sensitive IT-Instruments

The tools are clearly arranged in cases made from **conductive** black imitation leather, with zip fastener.

2251 Case with zip fastener, without tools

Outside dimensions: 190 x 135 x 35 mm (when closed)

2250 **BERNSTEIN** CARAT with tool set

9-piece set **conductive** tools from the series EUROline-Conductive to meet the most exacting standards.

Weight with tools: approx. 0.360 kg



Tool set:

No.	Description of individual tools
3-672-15	End cutters EUROline-Conductive , 130 mm, for copper wire up to 0.6 mm Ø, cutting edge 20° angular, box joint, double leaf spring, fine polished and bright burnished, conductive bicoloured hand-guard
3-683-15	Snipe nose pliers EUROline-Conductive , 130 mm, plain jaws, box joint, double leaf spring, fine polished and bright burnished, conductive bicoloured hand-guard
4-601	Screwdriver with conductive handle, blade from chrome vanadium, chrome-plated, with black tip, 50 x 0.8 mm
4-603	Screwdriver with conductive handle, blade from chrome vanadium, chrome-plated, with black tip, 50 x 1.5 mm
4-621	Cross-recess screwdriver size 000, with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
4-623	Cross-recess screwdriver size 0, with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
5-191	Tweezers , made from conductive and acid-resistant black plastic material, reinforced with glassfibre, 120 mm, with straight, rounded tips
6-661	TORX-screwdriver T 5, with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
6-663	TORX-screwdriver T 7, with conductive handle, blade from chrome vanadium, chrome-plated, with black tip

2270 **BERNSTEIN** ACCENT with tool set

9-piece set **conductive** tools with bright steel polished pliers

Weight with tools: approx. 0.360 kg

Tool set:

No.	Description of individual tools
3-601-13	Side cutters , 120 mm, for hard wire up to 0.4 mm Ø, for soft wire up to 1.0 mm Ø, bright steel-polished, box joint, double leaf spring, with conductive black hand-guard
3-633-13	Snipe nose pliers , 120 mm, plain jaws, bright steel-polished, box joint, double leaf spring, with conductive black hand-guard
4-601	Screwdriver with conductive handle, blade from chrome vanadium, chrome-plated, with black tip, 50 x 0.8 mm
4-603	Screwdriver with conductive handle, blade from chrome vanadium, chrome-plated, with black tip, 50 x 1.5 mm
4-621	Cross-recess screwdriver size 000, with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
4-623	Cross-recess screwdriver size 0, with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
5-191	Tweezers , made from conductive and acid-resistant black plastic material, reinforced with glassfibre, 120 mm, with straight, rounded tips
6-661	TORX-screwdriver T 5, with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
6-663	TORX-screwdriver T 7, with conductive handle, blade from chrome vanadium, chrome-plated, with black tip



3-680 **BERNSTEIN** EUROline-Conductive set of pliers

4-piece set **conductive** pliers from the series EUROline-Conductive to meet highest quality standards

Weight with tools: approx. 0.390 kg

Tool set:

No.	Description of individual tools
3-651-15	Mini side cutters EUROline-Conductive , 120 mm, without sideface, for soft wire up to 0.6 mm Ø, copper wire up to 1.2 mm Ø, box joint, double leaf spring, fine polished and bright burnished, conductive bicoloured hand-guard
3-672-15	End cutters EUROline-Conductive , 130 mm, for copper wire up to 0.6 mm Ø, cutting edge 20° angular, box joint, double leaf spring, fine polished and bright burnished, conductive bicoloured hand-guard
3-682-15	Flat nose pliers EUROline-Conductive , 130 mm, plain jaws, finish as before
3-683-15	Snipe nose pliers EUROline-Conductive , 130 mm, plain jaws, finish as before

