

EDU33210A Series Smart Bench Essentials Waveform and Function Generators



Rich in waveform capabilities

[Buy / Quote](#)

Already own this product? [View Technical Support](#)

Learn from experts and discover new test gear. [Re Live from the Lab](#)



[Highlights](#)

[Specifications](#)

[Models](#)

[Software, Accessories, Services](#)

[Resources](#)

HIGHLIGHTS

Entry Level Never Looked This Good

The Keysight EDU33210 Series function / arbitrary waveform generators bring uncompromising performance to an entry-level function generator. Get all the basic functions and waveforms with the most stable, lowest-distortion function generator in its class. Included features give you the capabilities and flexibility you need to get your job done quickly, no matter how complex. An intuitive, information-packed front-panel interface enables you to quickly resume where you left off. It offers the following features:

- USB and LAN input / output interfaces for remote connectivity
- 20 MHz sine and square waveforms
- ramp, triangle, noise, pulse generation with a variable edge, and DC waveform
- Keysight PathWave BenchVue software to enable remote instrument control
- Six built-in modulation types and 17 popular waveforms to simulate typical application for testing
- 7-inch color display for simultaneous parameter set up, signal viewing, and editing
- 16-bit arbitrary waveform capability with memory up to 8 M samples per channel



SMART BENCH ESSENTIALS SERIES

The EDU33210A Series smart bench essentials function generators are part of a family of four professional-grade instruments: a digital multimeter, power supply, function generator, and oscilloscope. You also get powerful remote connectivity software and KeysightCare 24/7 technical support. The PathWave software enables you to harness the power of four instruments in a single software interface. Easy setup provides quick control of your test hardware.

The Smart Bench Essentials family comes with intuitive lab tools to track and manage



your maintenance schedule to ensure all instruments are up to date. Test, analyze, and share results collaboratively — across the room or around the world.



Solution Brief

KEY SPECIFICATIONS

Max Bandwidth

20 Mhz

Max Arbitrary Waveform Length

1 Msa

Max Sample Rate


250 Msa/s


Harmonic Distortion

$1 V_{pp} \leq V_{out} \leq 10 V_{pp}$

Want to see more specifications?

FIND THE MODEL THAT'S RIGHT FOR YOU

<p>EDU33211A Waveform Generator, 20 MHz, 1 Channel</p> <p>The EDU33211A single channel function / arbitrary waveform generators brings uncompromising performance to an entry-level function generator.</p> <p>Get Quote</p> <p>MORE</p>	<p>EDU33212A Waveform Generator, 20 MHz, 2 Channel</p> <p>The EDU33212A dual channel function / arbitrary waveform generators brings uncompromising performance to an entry-level function generator.</p> <p>Get Quote</p> <p>MORE</p>	<p></p> <p>View and Compare All Models</p>
---	---	--



SIMPLIFY DATA GATHERING AND ANALYSIS

PathWave BenchVue function generator software for the PC enables control of Smart Bench Essentials function generators to set waveform properties and load custom arbitrary waveforms from files.

- Get easy-to-log data, screenshots, and system status.
- Replicate and save instrument configurations to repeat results.
- Achieve quick export of measurement data in the desired format

[Check Out PathWave BenchVue software](#)

ACCELERATE THE WIN WITH TECHNICAL SUPPORT

The Smart Bench Essentials instruments include KeysightCare support. You will have access to Keysight technical experts and a 24/7 knowledge center to help you get up to speed in the shortest amount of time.

What do you get?

- 2-business-day technical response
- online knowledge center
- self-service web portal

[Learn More About KeysightCare](#)



EXTEND THE CAPABILITIES OF YOUR EDU33210 FUNCTION / ARBITRARY WAVEFORM GENERATOR

Software

[See Related Software](#)

Accessories

[See Related Accessories](#)

Services

- [KeysightCare Service and Support >](#)
- [Calibration Services >](#)
- [Education Services >](#)
- [Technology Refresh Services >](#)
- [Financial Services >](#)

[See All Services](#)

Support

- [Resources >](#)
- [Drivers, Firmware & Software >](#)
- [Calibration and Repair >](#)
- [Training and Events >](#)

[See All Support](#)

FEATURED RESOURCES

White Papers 2020.06.05

Waveform Generators Increase Design Efficiency

Application Notes 2020.02.05

Waveform Sequencing with PathWave BenchVue Waveform Builder Pro

Application Notes 2018.08.12

How to Easily Create an Arbitrary Waveform Without Programming

White Papers 2020.04.22

4 Essential Methods for Creating and Editing Waveforms

Want help or have questions?

[Contact Us](#)

DISCOVER

[Products + Services](#)
[Solutions](#)
[Industries](#)
[Events](#)
[Keysight University](#)

ABOUT KEYSIGHT

[Newsroom](#)
[Investor Relations](#)
[Corporate Social Responsibility](#)
[Modern Slavery Act Transparency Statement](#)
[Careers](#)



EXPLORE

[Success Stories](#)
[Resources](#)
[Blog](#)
[Community](#)

PARTNERS

SUPPORT

[Keysight Product Support](#)
[Ixia Product Support](#)
[Manage Software Licenses](#)

MYKEYSIGHT