

N Male Crimp to TNC Male Crimp

multicompPRO


**RoHS
Compliant**



Specifications

Connector to Connector : N-Type Plug to TNC Plug
 Impedance : 50Ω
 Jacket Colour : Black

Diagram



No	Description	Material/Finish
1	N Male Crimp	Brass/ Nickel
2	TNC Male Crimp	
3	Strain Relief	Polyvinyl Chloride/Black
4	Tubing	*Heat Shrink/Black
5	Cable	-

*Dual Wall Polyolefin

Specification Table

Part Number	Length (Inches)	Cable Type	Strain Relief	Part Number	Length (Inches)	Cable Type	Strain Relief
SPC25301	12	RG-142B/U	No	SPC25635	48	RG-223/U	No
SPC25302	24	RG-142B/U	No	SPC25636	60	RG-223/U	No
SPC25304	36	RG-142B/U	No	SPC25637	72	RG-400/U	No
SPC25305	48	RG-142B/U	No	SPC25638	12	RG-400/U	No
SPC25306	60	RG-142B/U	No	SPC25639	24	RG-400/U	No
SPC25477	72	RG-58C/U	Yes	SPC25640	36	RG-400/U	No
SPC25479	12	RG-58C/U	Yes	SPC25641	48	RG-400/U	No
SPC25481	24	RG-58C/U	Yes	SPC25642	60	RG-400/U	No
SPC20834	36	RG-58C/U	Yes	SPC25649	72	RG-316/U	No
SPC25484	48	RG-58C/U	Yes	SPC25650	12	RG-316/U	No
SPC20835	60	RG-58C/U	Yes	SPC25651	24	RG-316/U	No
SPC25632	72	RG-223/U	No	SPC25652	36	RG-316/U	No
SPC25633	12	RG-223/U	No	SPC25653	48	RG-316/U	No
SPC25634	24	RG-223/U	No	SPC25654	60	RG-316/U	No
SPC24564	36	RG-223/U	No	SPC25303	72	RG-142B/U	No

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicompPRO

Part Number	Length (Inches)	Cable Type	Strain Relief	Part Number	Length (Inches)	Cable Type	Strain Relief
SPC27783	12	RG-316/U DS	No	SPC27831	12	RG-122/U	No
SPC27784	24	RG-316/U DS	No	SPC27832	24	RG-122/U	No
SPC27785	36	RG-316/U DS	No	SPC27833	36	RG-122/U	No
SPC27786	48	RG-316/U DS	No	SPC27834	48	RG-122/U	No
SPC27787	60	RG-316/U DS	No	SPC27835	60	RG-122/U	No
SPC27788	72	RG-316/U DS	No	SPC27836	72	RG-122/U	No
SPC27807	12	LMR-240	No	SPC27837	12	LMR-200	No
SPC27808	24	LMR-240	No	SPC27838	24	LMR-200	No
SPC27809	36	LMR-240	No	SPC27839	36	LMR-200	No
SPC27810	48	LMR-240	No	SPC27840	48	LMR-200	No
SPC27811	60	LMR-240	No	SPC27841	60	LMR-200	No
SPC27812	72	LMR-240	No	SPC27842	72	LMR-200	No
SPC27813	12	LMR-195	No	SPC27843	12	LMR-100	No
SPC27814	24	LMR-195	No	SPC27844	24	LMR-100	No
SPC27815	36	LMR-195	No	SPC27845	36	LMR-100	No
SPC27816	48	LMR-195	No	SPC27846	48	LMR-100	No
SPC27817	60	LMR-195	No	SPC27847	60	LMR-100	No
SPC27818	72	LMR-195	No	SPC27848	72	LMR-100	No
SPC27819	12	RG-174/U	No	SPC29103	12	RG-58A/U	Yes
SPC27820	24	RG-174/U	No	SPC29104	24	RG-58A/U	Yes
SPC27821	36	RG-174/U	No	SPC29105	36	RG-58A/U	Yes
SPC27822	48	RG-174/U	No	SPC29106	48	RG-58A/U	Yes
SPC27823	60	RG-174/U	No	SPC29107	60	RG-58A/U	Yes
SPC27824	72	RG-174/U	No	SPC29108	72	RG-58A/U	Yes
SPC27825	12	RG-188A/U	No	SPC27801	12	RG-8/X	No
SPC27826	24	RG-188A/U	No	SPC27802	24	RG-8/X	No
SPC27827	36	RG-188A/U	No	SPC27803	36	RG-8/X	No
SPC27828	48	RG-188A/U	No	SPC27804	48	RG-8/X	No
SPC27829	60	RG-188A/U	No	SPC27805	60	RG-8/X	No
SPC27830	72	RG-188A/U	No	SPC27806	72	RG-8/X	No

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.