5205817-4 - ACTIVE


AMPLIMITE | AMPLIMITE Kit

TE Internal #: 5205817-4 AMPLIMITE Kit, D-Sub Locking & Mounting, Female Screwlock Assembly Kit, Screw Length .5 in [12.7 mm]

View on TE.com >



Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: Female Screwlock Assembly Kit

Screw Length: 12.7 mm [.5 in]

Features

Product Type Features

Product Type

Accessory

D-Shaped Connector Accessories

Female Screwlock Assembly Kit

Mechanical Attachment

Screw Plating Material	Zinc			
Screwlock Style	Screwlock with Lockwasher and Hex Nut			
Screw Material	Steel			
Screw Finish	Clear Chromate			
Screw & Hole Thread Size	4-40 UNC			
Screw Length	12.7 mm[.5 in]			
Dimensions				
Thread Length	7.92 mm[.312 in]			
Operation/Application				
For Use With	Metal Shell or All Plastic Connectors (HDP or HDF)			
Packaging Features				
Packaging Quantity	500			
Packaging Method	Bag, Kit			

5205817-4

AMPLIMITE Kit, D-Sub Locking & Mounting, Female Screwlock Assembly Kit, Screw Length .5 in [12.7 mm]



Product Compliance For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions	
EU ELV Directive 2000/53/EC	Compliant with Exemptions	
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold	
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.35% in Component Part) Aticle Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.	
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free	
Solder Process Capability	Not applicable for solder process capability	

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




Also in the Series | AMPLIMITE Kit

C For support call+1 800 522 6752


5205817-4

AMPLIMITE Kit, D-Sub Locking & Mounting, Female Screwlock Assembly Kit, Screw Length .5 in [12.7 mm]





Customers Also Bought



HDP-22,RCPT,SIZE 5,78 POSN	2064 0000 00	AMPLIMITE,ASY,PLUG,STD,109,ZN,3	2031 5002 00
TE Part #91287-1 TOOL,T-HANDLE	TE Part #1-1337421-0 BNC Str Plg MC 50Ohm Silver Pl		

Documents

Product Drawings FEMALE SCREWLOCK KIT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5205817-4_A.2d_dxf.zip

5205817-4

AMPLIMITE Kit, D-Sub Locking & Mounting, Female Screwlock Assembly Kit, Screw Length .5 in [12.7 mm]



English

Customer View Model ENG_CVM_CVM_5205817-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5205817-4_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Environmental Compliance TE Material Declaration

English

Instruction Sheets Instruction Sheet (U.S.)

English