





KX0604/STN
KX0603/STN
with PNo 11990/Col. fitted



KX0605/STN
with PNo 11990/Col. fitted




KX0607
KX0606



KX0608



Data	List No.	KX0603/STN	KX0604/STN	KX0605/STN	KX0606	KX0607	KX0608
Ø:		19.8	26.2	33.7	14.0	21.0	28.1
Height:		15.9	15.9	15.9	16.5	20.3	24.1
Shaft:		Ø: 6.4 Length: 12.7	Ø: 6.4 Length: 12.7	Ø: 6.4 Length: 12.7	Ø: 6.4 Length: 8.9	Ø: 6.4 Length: 9.3	Ø: 6.4 Length: 22.6
Nut Recess:		Ø: 16.7 Depth: 1.6	Ø: 20.2 Depth: 1.6	Ø: 27.8 Depth: 1.6	Ø: 11.0 Depth: 2.4	Ø: 17.5 Depth: 2.8	Ø: 24.5 Depth: 2.8
Radius to Pointer:		13.5 (with P.No.11990 fitted).	17.1 (with P.No.11990 fitted).	20.2 (with P.No.11990 fitted).			
Decor Discs: (Aluminium)		Satin (Matt) Finish	Satin (Matt) Finish	Satin (Matt) Finish			
Fixing:		Slotted head grub screw. (Allen key to agreed order).			Slotted head grub screw. (Allen key to agreed order).		
Mouldings:		Phenolic.	Phenolic.	Phenolic.	Thermoplastic.	Thermoplastic.	Thermoplastic.
Inserts:		Brass, Nickel Plated.	Brass, Nickel Plated.	Brass, Nickel Plated.	Brass, Nickel Plated.	Brass, Nickel Plated.	Brass, Nickel Plated.
Grub Screws:		Steel, Zinc Passivated.	Steel, Zinc Passivated.	Steel, Zinc Passivated.	Steel, Zinc Passivated.	Steel, Zinc Passivated.	Steel, Zinc Passivated.
Variants:		Other shafts, colours and indicator lines (/IL) may be available to agreed order. Pointer P.No. 11990/Col (/BK - black, /WH - white, /GN - green, /RD - red) to be ordered separately.			Other shafts, colours and indicator lines (/IL) may be available to agreed order.		




KX0370



KX0370 & KX0372



KX0107



KX0357



KX0522



Data	List No.	KX0370	KX0370 & KX0372	KX0107	KX0357	KX0522
Ø:		31.8	47.6			13.5
Height:		14.3	17.5	12.7	15.9	16.7
Shaft:		Ø: 6.4 Length: 9.5	Ø: 6.4 Length: 12.8	Ø: 6.4 Length: 9.5	Ø: 6.4 Length: 11.9	Ø: 6.4 Length: 6.8
Nut Recess:			Ø: 18.3 Depth: 3.2	Ø: 14.3 Depth: 1.6	Ø: 15.9 Depth: 2.4	
Radius to Pointer:		19.8		15.9	15.9	
Decor Discs:						
Fixing:		Slotted head grub screw. (Allen key to agreed order).		Slotted head grub screw. (Allen key to agreed order).		Collet.
Mouldings:		Phenolic.	Phenolic.	Phenolic.	Phenolic.	Thermoplastic.
Inserts/Collet:		Brass, Nickel Plated.	Brass, Nickel Plated.	Brass, Nickel Plated.	Brass, Nickel Plated.	Aluminium, Black Anodised.
Grub Screws/Nut:		Steel, Zinc Passivated.	Steel, Zinc Passivated.	Steel, Zinc Passivated.	Steel, Zinc Passivated.	Brass, Nickel Plated.
Variants:		Other shafts, colours and indicator lines (/IL) may be available to agreed order.		Other shafts, colours and indicator lines (/IL) may be available to agreed order.		