Powercon True Top Cable Assemblies

multicomp PRO

Component Parts

Connectors - Neutrik Powercon True1 - TOP

- Heavy duty sealed power connector for harsh and demanding environment
- IP65 rating and certified outdoor protection to UL 50E enclosure type 4 (in mated condition)
- Uses high impact UV-resistant materials
- True mains connector with breaking capacity (CBC)
- Lockable 16 A single phase connector (USA: 20 A)
- · Easy and reliable twist lock system
- Extremely robust and reliable
- Unique Neutrik cable retention

• ENEC certified according to IEC 60320

Cable - Titanex 3mm × 2.5mm HO7RNF

Description	: Industrial flexible cable, insulation and outer sheath in elastomer.
	Oil resistant, flame retardant according to IEC/EN 60332-1-2 standard.
Standards	: International : EN 50525-2-21; HD 22.4; HD 516; IEC 60245-4 type 66
National	: NF C 32-102-4

Product Listing

MP007873	Powercon True 1M- F 3mm × 2.5mm HO7RNF 0.5M
MP007878	Powercon True 1 M- F 3mm × 2.5mm HO7RNF 1M
MP007879	Powercon True 1 M- F 3mm × 2.5mm HO7RNF 2M
MP007875	Powercon True 1 M- F 3mm × 2.5mm HO7RNF 3M
MP007874	Powercon True 1 M- F 3mm × 2.5mm HO7RNF 5M
MP007876	Powercon True 1 M- F 3mm × 2.5mm HO7RNF 10M
MP007877	Powercon True 1 M- F 3mm × 2.5mm HO7RNF 15M
MP007880	Powercon True 1 M- F 3mm × 2.5mm HO7RNF 20M
MP007881	Powercon True 1 M- F 3mm × 2.5mm HO7RNF 30M

Part Number Table

Description	Part Number
Powercon True Top Cable Assembly, Male to Female, 3mm x 2.5mm, 0.5m	MP007873
Powercon True Top Cable Assembly, Male to Female, 3mm x 2.5mm, 10m	MP007878
Powercon True Top Cable Assembly, Male to Female, 3mm x 2.5mm, 15m	MP007879
Powercon True Top Cable Assembly, Male to Female, 3mm x 2.5mm, 2m	MP007875
Powercon True Top Cable Assembly, Male to Female, 3mm x 2.5mm, 1m	MP007874
Powercon True Top Cable Assembly, Male to Female, 3mm x 2.5mm, 3m	MP007876
Powercon True Top Cable Assembly, Male to Female, 3mm x 2.5mm, 5m	MP007877
Powercon True Top Cable Assembly, Male to Female, 3mm x 2.5mm, 20m	MP007880
Powercon True Top Cable Assembly, Male to Female, 3mm x 2.5mm, 30m	MP007881

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



RoHS Compliant