

GRM31C5C2A104JA01#

Note: This datasheet may be out of date.

Please download the latest datasheet of GRM31C5C2A104JA01# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=GRM31C5C2A104JA01%23

"#" indicates a package specification code.


















< List of part numbers with package codes > GRM31C5C2A104JA01L GRM31C5C2A104JA01K



Appearance & Shape







References

Packaging	Specifications	Standard
		Packing
		Quantity
L	180Embossed Tape	2000
K	330Embossed Tape	6000

Mass (typ.)		
1 piece	38.0mg	
φ180mm Reel	116g	



Derating1

1 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





GRM31C5C2A104JA01#

Note: This datasheet may be out of date.

Please download the latest datasheet of GRM31C5C2A104JA01# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=GRM31C5C2A104JA01%23

"#" indicates a package specification code.



Specifications

Length	3.2±0.2mm
Width	1.6±0.2mm
Thickness	1.6±0.2mm
Capacitance	0.10µF ±5%
Distance between external terminals g	1.5mm min.
External terminal size e	0.3 to 0.8mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	100Vdc
Size code in inch(mm)	1206 (3216M)
тс	0±30ppm/°C
Temperature characteristics (complied standard)	C0G(EIA)
Temperature range of temperature characteristics	25°C to 125°C

2 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Product Search Data Sheet

Note: This datasheet may be out of date. Please download the latest datasheet of GRM31C5C2A104JA01# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=GRM31C5C2A104JA01%23


"#" indicates a package specification code.


GRM31C5C2A104JA01#





Characteristic Data

The charts below may show another part number which shares its characteristics.









GRM31C5C2A104JA01 C-DC bias capchange, 25.0degC, AC1V

3 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering







Note: This datasheet may be out of date. Please download the latest datasheet of GRM31C5C2A104JA01# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=GRM31C5C2A104JA01%23

"#" indicates a package specification code.

GRM31C5C2A104JA01#





4 of 4

Attention

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

