

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [2175112102](#)  
**Status:** **Active**  
**Overview:** [Off-the-Shelf Pre-Crimped Leads](#)  
**Description:** Pre-Crimped Lead L1NK 250 Female-to-L1NK 250 Female, Tin (Sn) Plating, 150.00mm Length, 26 AWG, Red



**Documents:**  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Datasheet \(PDF\)](#)

**General**  
Product Family Cable Assemblies  
Series [217511](#)  
Assembly Configuration Pre-crimped Lead Only  
Connector to Connector L1NK 250 Crimp Terminals  
Overview [Off-the-Shelf Pre-Crimped Leads](#)  
Product Name L1NK 250  
UPC 195842119666

**Physical**  
Cable Length 150.00mm  
Circuits (Loaded) 1  
Color - Resin Red  
Gender Female-Female  
Material - Metal Copper Alloy  
Material - Plating Mating Tin  
Material - Plating Termination Tin  
Material - Resin PVC  
Net Weight 0.524/g  
Packaging Type Bag  
Single Ended No  
Termination Interface: Style Crimp or Compression  
Wire Insulation Diameter 1.42mm-1.60mm  
Wire Size AWG 26  
Wire/Cable Type UL 1569

**Electrical**  
Current - Maximum per Contact 6.5A  
Voltage - Maximum 250V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**  
Sales Drawing 2175112101-000

**EU ELV**  
**Not Relevant**

| <b>EU RoHS</b>                                                | <b>China RoHS</b> |
|---------------------------------------------------------------|-------------------|
| <b>Compliant</b>                                              |                   |
| <b>REACH SVHC</b>                                             |                   |
| Not Contained Per - D(2021)4569-DC (8 July 2021)              |                   |
| <b>Halogen-Free</b>                                           |                   |
| <b>Status</b>                                                 |                   |
| <b>Not Low-Halogen</b>                                        |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Green Image       |
| ELV                                                           | Not Relevant      |
| RoHS Phthalates                                               | Not Contained     |

**Search Parts in this Series**  
[217511](#) Series

**Use With**  
L1NK 250 Receptacle Housing [207841](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION