

# Wiha SYSTEM 4.

A Real Multi-tasker and Ideal for Precision Work.

## SYSTEM 4 Reversible Blades, Bit Holder, Nut Driver.



**269** SYSTEM 4 Combined Ballpoint Hex-Hex Reversible Blade.  
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.  
 Colour-coded Wiha ChromTop® tips.  
 Extra: The ballpoint enables the user to work at angles up to 25°.

Order-No.	⊙	⊕	↔	⬠	⬢	£
00582 5	1.3	1.3	120	4.0	5	5.30
00583 2	1.5	1.5	120	4.0	5	5.30
00584 9	2	2	120	4.0	5	5.30
00585 6	2.5	2.5	120	4.0	5	5.30
00586 3	3	3	120	4.0	5	5.20
00587 0	4	4	120	4.0	5	5.20



**U759 00** SYSTEM 4 Bit Holder.  
 Suitable for C 4 (4 mm) Bits.  
 Blade: Chrome-vanadium steel, through hardened, electro-plated.

Order-No.	⊙	↔	⬠	⬢	£
09195 8	4.0	135	4.0	1	6.90



**269** SYSTEM 4 Nut Driver.  
 For Hex Nuts.  
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.  
 Application: For hex nuts.


Order-No.	⊙	⊕	↔	⬠	⬢	£
00588 7	1.5	1.8	125	4.0	5	5.30
00589 4	2	2.5	125	4.0	5	5.30
00590 0	3		125	4.0	5	4.40
00591 7	3.2		125	4.0	5	4.40
00592 4	3.5		125	4.0	5	4.40
00593 1	4		125	4.0	5	4.40
00594 8	4.5		125	4.0	5	4.40
00595 5	5		125	4.0	5	4.40
00596 2	5.5		125	4.0	5	4.40

## SYSTEM 4 Set in Metal Box.



**NEW**  
**7000 EB16** SYSTEM 4 Bit Set, 16 pcs.  
 With Bit Holder and 14 Slotted/ Phillips/ TORX®/ Hex C 4 Bits.  
 Handle: SYSTEM 4 SoftFinish®-telescopic handle.  
 Enables adjustable bit holder blade length.  
 Standards: DIN 3126, ISO 1173, style C 4.  
 Application: The universal set for all precision assembly work.

Order-No.	Series	⬢	£
27872 4	7000 EB16	1	43.40
	2691	SYSTEM 4 SoftFinish®-telescopic handle	
	U759 00	4.0x135	
⊙	U 750	1.5x0.25	2.0x0.4 3.0x0.5 4.0x0.8
⊕	U 751	PH00x28	PH0x28 PH1x28
⬠	U 757	T6x28	T8x28 T10x28 T15x28
⬢	U 753	2.0x28	2.5x28 3.0x28



*Practical and compact:  
 select the appropriate blade – insert it into  
 the handle – that's all there is to it!*