

Slotted/ Phillips and Slotted/ Pozidriv Sets.



148 HK5 Classic Slotted/Phillips Screwdriver Set, 5 pcs.
Round Blades.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Anti-Cam-Out ribs on tip sizes 5.5 / 7.0.
Handle: Impact, oil and grease resistant Wiha Classic handle.
Application: For universal use in trade and industry.

Order-No.	Series				£
00105 6	148 HK5	1			21.00
⓪	148	4.5x100	5.5x120	7.0x140	
⊕	153	PH1x80	PH2x100		



148 ZK5 Classic Slotted/Pozidriv Screwdriver Set, 5 pcs.
Round Blades.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Anti-Cam-Out ribs on tip sizes 5.5 / 7.0.
Handle: Impact, oil and grease resistant Wiha Classic handle.
Application: For universal use in trade and industry.

Order-No.	Series				£
00108 7	148 ZK5	1			23.20
⓪	148	4.5x100	5.5x120	7.0x140	
⊕	222	PZ1x80	PZ2x100		

Slotted and Phillips Screw-holding Screwdrivers.



390 Classic Slotted Screw-holding Screwdriver.
Spread Blade Holds the Screw.

Blade: Chrome-vanadium steel, through hardened, zinc-plated.
Sliding sleeve with coating.
Handle: Impact, oil and grease resistant Wiha Classic handle.
Application: For setting and turning screws in areas that are difficult to access.

Order-No.	⓪	⓪	↔	↔	↔	£
01483 4	0.4	5.0	90	175	22	12.00
01485 8	0.6	3.5	125	220	24	13.00
01486 5	0.6	3.5	175	270	24	13.20
01488 9	0.6	5.5	125	220	24	13.20
01489 6	0.6	5.5	175	270	24	13.80
01491 9	0.8	5.5	130	225	24	13.90
01492 6	0.8	5.5	180	275	24	14.40
01494 0	1.2	8.0	190	295	28	14.60



395 Classic Phillips Screw-holding Screwdriver.
Clamping Sleeve Holds the Screw.

Blade: Chrome-vanadium steel, through hardened, black-finish.
Clamping sleeve made of high-quality polyamide.
Handle: Impact, oil and grease resistant Wiha Classic handle.
Application: For setting and turning screws in areas that are difficult to access.

Order-No.	⊕	↔	↔	↔	£
01502 2	PH0	100	195	24	10.90
01503 9	PH1	125	230	28	13.20
01504 6	PH2	175	290	32	15.30