

Wiha Hex L-Keys.

Metric Sizes.

Ballpoint Hex L-Keys.



369 Ballpoint Hex L-Key, Long.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Standards: Profile, length and hardness according to ISO 2936L.
 Application: Especially for screws that are difficult to access.
 Extra: The ballpoint enables the user to work at angles up to 25°.

Order-No.	●	↔	└┘	≡	£
01392 9	1.5	91	15	10	0.86
01393 6	2	101	18	10	0.86
01395 0	2.5	113	20	10	0.91
01396 7	3	128	23	10	0.95
01398 1	4	142	29	10	1.29
01400 1	5	163	33	10	1.46
01402 5	6	184	38	10	1.85
07922 2	7	195	39	5	2.90
01404 9	8	206	44	10	3.10
01406 3	10	231	50	5	4.15
01408 7	12	259	57	5	5.70

SB 369 Ballpoint Hex L-Key, Long.
 Blister Packed.

Order-No.	●	↔	└┘	≡	£
08161 4	1.5	91	15	10	1.73
08162 1	2	101	18	10	1.81
08163 8	2.5	113	20	10	1.85
08164 5	3	128	23	10	1.96
08165 2	4	142	29	10	2.19
08166 9	5	163	33	10	2.30
08167 6	6	184	38	10	2.81
08168 3	8	206	44	5	3.81
08169 0	10	231	50	5	4.90
08170 6	12	259	57	5	6.50

Ballpoint Hex L-Keys Sets and Display.



369 S9 Ballpoint Hex L-Key Set in ProStar.
 Chrome-plated, 9 pcs.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Standards: Profile, length and hardness according to ISO 2936L.
 Application: Especially for screws that are difficult to access.
 Extra: Space saving ProStar allows the easy removal of each key without moving any others.
 The ballpoint enables the user to work at angles up to 25°.

Order-No.	≡	£
07185 1	369 S9	5 18.10
●	369	1.5 2 2.5 3 4 5 6 8 10

SB 369 S9 Ballpoint Hex L-Key Set in ProStar.
 Chrome-plated, 9 pcs.
 Blister Packed.

Order-No.	≡	£
07192 9	SB 369 S9	5 17.30
●	369	1.5 2 2.5 3 4 5 6 8 10



369 SVH1 Display Ballpoint Hex L-Key Sets.
 Chrome-plated, in ProStar, 9 pcs.
 Carton Display with 10 Pieces.

Order-No.	Content	●	≡	£
07194 3	10 x 369 S9	1.5 - 10	1	180.60