

NETWORK 2700 SERVICE SET

The set with all essential tools for the assembly and maintenance of networks



2700 **BERNSTEIN** NETWORK with tool set

2701 Case with zip fastener, without tools

Description:

In an elegant black nylon case with zip fastener and velvet grey lining 23 special tools are clearly arranged in pockets.

Outside dimensions: 320 x 250 x 100 mm (when closed)

Weight with tools: 2.750 kg

Tool set:

No.	Description of individual tools	No.	Description of individual tools
2-601	IC-tweezers, nickel-plated , 125 mm, for gripping, inserting and removing IC's	5-161	Clamping scissors , 130 mm, stainless, with serrated gripping jaws
3-125-1	Micro side cutters , 110 mm, for soft wire up to 0.8 mm and hard wire up to 0.3 mm, chrome-plated, with BERNSTEINIT-insulation	5-0601	Rotary coaxial cable stripper for cable types RG 58, RG 59 and RG 62
3-235-1	Telephone pliers , 145 mm, chrome-plated, with BERNSTEINIT-insulation	4-775	Plastic sprung handle for socket wrenches
3-815-1	Wire strippers , 155 mm, with adjusting screw for all wire thicknesses, chrome-plated, with BERNSTEINIT-insulation	6-203	Socket wrench , 6.0 mm, chrome vanadium, nickel plated, without handle
3-0605	Combination-crimping pliers for connector types, 6P/6C, 6P/4C, 6P/2C, 8P/8C	6-205	Socket wrench , 8.0 mm, chrome vanadium, nickel plated, without handle
3-0611	Crimping pliers for BNC- and TNC-coaxial connectors	6-207	Socket wrench , 10.0 mm, chrome vanadium, nickel plated, without handle
4-141	Screwdriver with special square BERNSTEIN handle, blade made from chrome vanadium, 75 x 3.5 mm, chrome-plated, with black tip	6-772	Adjustable wrench , chrome vanadium, 150 mm, jaw opening 0 - 18 mm
4-143	Screwdriver as above, 125 x 5.5 mm, chrome-plated, with black tip	6-965 L	TORX-Screwdriver , size T 10, with bore-hole in the tip, with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, black tip
4-255	Cross-recess screwdriver size 0, with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, with black tip, blade length 60 mm	6-966 L	TORX-Screwdriver , size T 15, as above, with bore-hole in the tip
4-256	Cross-recess screwdriver size 1, as above, blade length 80 mm	6-967 L	TORX-Screwdriver , size T 20, as above, with bore-hole in the tip
4-257	Cross-recess screwdriver size 2, as above, blade length 100 mm	8-390	Desoldering pump , 195 mm long, 20 mm Ø
		8-396	Gas soldering iron , 10 - 60 W