


# Tungsten Halogen


Lamps for spot/fog & headlights




Reference No	Volt	Watt	Type	Dim(mm)
<b>H1</b>				
<b>465</b>	6v	55w	H1	P14.5s
<b>448</b>	12v	55w	H1	P14.5s
<b>448XB</b>	12v	55w	H1 X/Blue	P14.5s
<b>448XP</b>	12v	55w	H1 X/+60%	P14.5s
<b>481</b>	12v	100w	H1	P14.5s
<b>491</b>	12v	130w	H1	P14.5s
<b>461</b>	24v	100w	H1	P14.5s
<b>466</b>	24v	70w	H1	P14.5s
• <b>466HD</b>	24v	70w	H1	P14.5s




<b>H2</b>				
<b>479</b>	12v	55w	H2	X511
<b>482</b>	12v	100w	H2	X511
<b>492</b>	12v	130w	H2	X511
<b>480</b>	24v	70w	H2	X511
<b>462</b>	24v	100w	H2	X511



<b>H3</b>				
<b>455</b>	6v	55w	H3	PK22s
<b>453</b>	12v	55w	H3	PK22s
<b>454</b>	12v	35w	H3	PK22s
<b>483</b>	12v	100w	H3	PK22s
<b>493</b>	12v	130w	H3	PK22s
<b>460</b>	24v	70w	H3	PK22s
<b>463</b>	24v	100w	H3	PK22s
<b>442</b>	48v	45w	H3	PK22s



<b>H4</b>				
<b>444</b>	12v	35/35	HS1	Px43t-38
<b>472</b>	12v	60/55	H4	P43t
<b>472A</b>	12v	60/55	H4Amber	P43t
<b>472S</b>	12v	60/55	H4Seasons	P43t
<b>472XB</b>	12v	60/55	H4 X/Blue	P43t
<b>472XP</b>	12v	60/55	H4 X/+60%	P43t
<b>484</b>	12v	100/80	H4	P43t
<b>494</b>	12v	130/90	H4	P43t
<b>473</b>	12v	100/55	H4	P43t
<b>475</b>	24v	75/70	H4	P43t
<b>475S</b>	24v	75/70	H4 Seasons	P43t
<b>475XB</b>	24v	75/70	H4 X/Blue	P43t
• <b>475HD</b>	24v	75/70	H4	P43t
<b>496</b>	24v	100/80	H4	P43t
* <b>140180</b>	12v	60/35	H4	Alt.Lug
* <b>140339</b>	12v	65/55	3Lug	BA20



• Heavy Duty

\* Motorcycle Specials