

[Sign-up](#)[Careers](#)[Contact Us](#)[Products](#)[Where to Buy](#)[Media Center](#)[Tradesman Club](#)[Support](#)[About Klein](#)

[Home](#) » [Catalog](#) » [Personal Protection & Safety](#) » [Protective Equipment](#) » [Hard Hat Accessories](#)



Intrinsically Safe LED Headlamp 60156

★★★★★ (0) [Write a review](#)

- Standards tested: UL913 7th edition (US and Canada), CSA 22.2 No. 157-92, Reaffirmed 2012, CLASS I, DIV 1 and 2, C ABCD; CLASS II, DIV 1 and 2, GRP EFG; CLASS III; TEMP CODE: T4
- Intrinsically safe LED headlamp attaches directly to Klein® Hard Hats and Safety Helmets equipped with Klein accessor mount
- Mode / Lumens / Runtime: 216 lumens on high for 5 hours; lumens on low for 12 hours
- Powered by 3 x AAA batteries (included)
- IP67 rated: waterproof and dust proof
- Impact resistant: drop-test rated up to 6.6 feet (2m)
- Bracket tilt angle up to 70 degrees on hard hats (max 90 degrees)
- Pressure relief valve (on bottom)
- Large power / mode button
- Includes 1-inch (2.5 mm) Hex Key for covered battery compartment

[BUY ONLINE](#)[FIND LOCAL RETAILER](#)[PRODUCT MEDIA](#)[SPECIFICATIONS](#)[WARNINGS](#)[ACCESSORIES](#)[RELATED ITEMS](#)[REVIEWS](#)

DOWNLOADS

[Brochure](#)[Instructions](#)

IMAGES

JPG (High Resolution): [60156_photo.jpg](#)

PNG (Transparent Background): [60156.png](#)

This Intrinsically Safe Class I, II, and III / Division 1 Spot Headlamp is designed for hazardous locations, where explosion risk due to fine dust or fumes is high. This headlamp is designed to deliver an optimal combination of lightweight, IP rated waterproof and dust proof rugged construction. Powered by 3 x AAA batteries, this intrinsically safe LED headlamp mounts directly on front or back accessory mounts found exclusively on Klein® Hard Hats and Safety Helmets; strap needed! Please consult your safety supervisor before using this product.

Specifications

Type: Headlamp

Battery Life: High: 5 hr; Low: 12 hr

Application: Designed for Hazardous Environments

Batteries: 3 x AAA



Search Klein 

[Sign-up !\[\]\(3dfb8d66e81160ad61421a3452093d1b_img.jpg\)](#) [Careers](#) [Contact Us](#)

Products

Where to Buy

Media Center

Tradesman Club

Support

About Klein

Overall Length:	1.9" (4.8 cm)	Drop Protection:	6.6' (2 m)
Overall Height:	2.44" (6.2 cm)	Standard:	CLASS I DIV 1 and 2 GRP ABCD; CLASS II DIV 1 and 2 GRP EFG; CLASS III; TEMPERATURE CODE T4
Overall Width:	3.31" (8.4 cm)	Included:	Hex Key, Batteries
Material:	PC/TPU	Weight:	3.68 oz (104 g)
Lumens:	High: 216; Low: 75	UPC:	092644601569
Bulb Type:	LED		

Additional Information

WARRANTY

WARNINGS

- Read, understand and follow instructions to ensure safe operation.
- Please consult your safety supervisor before using this product.

ACCESSORIES



60145
Safety Helmet, Non-Vented-Class E, White
★★★★★ 0.0 (0)



60401
Hard Hat, Vented, Full Brim Style, White
★★★★★ 5.0 (2)

RELATED ITEMS

