

KERN MPS200K100M



Professional personal floor scale with BMI function as well as EC type approval and approval for medical use for professional use in medical diagnostics



Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Battery:	6x1.5 V AA
Charging time:	14 h
Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK
Operating time:	50 h
Operating time (Backlight off):	35 h
Rechargeable battery:	Rchrg. battery optional - intern

Measuring system

Adjustment options:	External calibration
Linearity:	100 g
Readability [d]:	100 g
Recommended adjusting weight:	200 kg (M1)
Repeatability:	100 g
Resolution:	2000
Warm up time:	10 min
Weighing capacity [Max]:	200 kg
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height (large):	2,500 cm
-------------------------------	----------

Technical data about verification

Minimum load [Min]:	2 kg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	100 g

Functions

BMI function:	yes
Data hold function:	yes
PRE-TARE function:	yes
Vibration-free weighing (Animal weighing program):	yes

Services (optional)

Adjustment at the location of installation:	961-249
DAkkS Certificate:	963-129
Verification:	965-129

Category

Brand:	KERN
Category:	Balances
Product Group:	Personal floor scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	370 x 510 x 110 mm
Gross weight:	5,700 kg
Net weight:	4,100 kg
Shipping method:	Parcel service

Construction

Cable length:	1,800 m
Cable length of display device:	1,210 m
Casing material:	Steel lacquered
Dimensions of display device (WxDxH):	216 x 110 x 47 mm
Dimensions of weighing plate (WxDxH):	275 x 295 x 58 mm
Level indicator:	yes
Material weighing plate:	Steel lacquered
Overall dimensions mounted (WxDxH):	275 x 295 x 58 mm
Revolving screw feet:	yes
Wall mount:	yes

KERN MPS200K100M



Professional personal floor scale with BMI function as well as EC type approval and approval for medical use for professional use in medical diagnostics

Piktogramme

STANDARD



OPTION



FACTORY

