



Invincible Faceshields

A range of faceshields which users can tailor to meet to the hazardous situation at hand. All items can be purchased separately to suit personal requirements.

Faceshields can be bound with aluminium for added strength and durability or a chinguard can be fitted for added protection. Visors can be attached to helmets with a Cliptite Attachment kit.

- Choose a polycarbonate visor for protection against impact
- Choose an acetate visor for protection against liquid or chemical splash
- Choose a wire gauze visor for protection against large low speed flying particles
- Choose a green gas weld shade 5 visor for protection whilst gas welding
- Faceshields Consist of: Browguard, Visor, Optional, Chinguard

Product	Code	Description
<u>Invincible Yellow Chinguard and Browguard</u>	AFB012-310-200	6"/15cm Yellow Chin and Browguard Acetate
<u>Invincible Yellow Chinguard and Browguard</u>	AFB011-330-200	8"/20cm Yellow Chin and Browguard Acetate
<u>Invincible Yellow Browguard</u>	AFA011-210-200	6" /15cm Yellow Browguard Acetate-Unbound
<u>Invincible Yellow Browguard</u>	AFA101-110-200	6"/15cm Yellow Browguard Wire Gauze/Bound
<u>Invincible Yellow Browguard</u>	AFA011-110-200	6"/15cm Yellow Browguard Acetate-Bound
<u>Invincible Yellow Browguard</u>	AFA011-130-200	8" /20cm Yellow Browguard Acetate-Bound
<u>Invincible Yellow Browguard</u>	AFA011-150-200	10"/25cm Yellow Browguard Acetate-Bound
<u>Invincible Yellow Browguard</u>	AFA021-130-200	8"/20cm Yellow Browguard Acetate GW5-Bound
<u>Invincible Black Chin Strap and Browguard</u>	AFB062-331-100	8"/20cm Black Chin and Browguard Polycarbonate
<u>Invincible Black Browguard</u>	AFA061-111-100	6"/15cm Black Browguard Polycarbonate-Bound

<u>Invincible Black Browguard</u>	AFA061-131-100	8"/20cm Black Browguard Polycarbonate-Bound
<u>Invincible Clear Chinguard and Browguard</u>	AFB062-311-300	6"/15cm Clear Chin and Browguard Polycarbonate
<u>Invincible Clear Chinguard and Browguard</u>	AFB061-331-300	8"/20cm Clear Chin and Browguard Polycarbonate
<u>Invincible Yellow Browguard</u>	AFA101-130-200	8"/20cm Yellow Browguard Wire Gauze/Bound
<u>Invincible Yellow Browguard</u>	AFA021-130-200	8"/20cm Yellow Browguard Acetate GW5-Bound