GPS Active Internal Patch

APAM1866YA18

RoHS/RoHS II compliant

18.0 x 18.0 x 7.0mm

MSL level: N/A

18.0 v 18.0 v 7.0mm

FEATURES:

- Compact Size
- Easy to Install
- RoHS Compliant

> TYPICAL APPLICATIONS:

- Automotive Navigation, Marine buoys
- Personal Tracking
- Surveying equipment, Cell phone, Laptop
- Healthcare and medical monitoring devices, PND, PDA

> STANDARD SPECIFICATIONS:


Antenna

| Parameters | Min. | Тур. | N | Max. | Units | Note |
|-------------------------|------|-------------------|---|------|-------|--|
| Center Frequency | 157 | 75.42 ± 1.023 | 3 | | MHz | |
| Bandwidth | 8 | | | | MHz | |
| Gain | | 2.5 | | | dBic | (Peak gain on70*70mm Ground Plane facing Zenith.) |
| VSWR @ Center Frequency | | 2.0 | | | | |
| Polarization Model | | RHCP | | | | (Right Hand Circular Polarization) |
| Impedance | | 50 | | | Ω | |
| Working Temperature | -40 | | · | +85 | °C | |
| Storage Temperature | -40 | | | +85 | °C | |


Low Noise Amplifier (LNA)

| Parameters | Min. | Typ. | Max. | Units | Note |
|-------------------|------|------------------|------|-------|-----------------------------|
| Center Frequency | 1 | 575.42 ± 1.0 |)23 | MHz | |
| DC Voltage | 2.70 | 3.0 | 3.30 | V | |
| Gain | 24 | 27 | 30 | dB | (Without cable +25°C± 10°C) |
| Output VSWR | | | 2.0 | | |
| Noise Figure | | | 2.0 | dB | |
| DC current | 11 | 13 | 15 | mA | (At 3.0V) |
| Outband Rejection | 20 | | | dB | f0 + 100 MHz |
| (Absolute value) | 30 | | | dB | f0 - 100 MHz |

SMITH CHART



□ GPS LNA GAIN PLOT






5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com REVISED: 08.03.2018

ABRACON IS ISO9001-2015 CERTIFIED


GPS Active Internal Patch

APAM1866YA18

RoHS/RoHS II compliant







PACKAGING

| | | 328 |
|--------------|--|--------|
| Package Type | Quantity | |
| MOQ | 150 pcs | |
| Tray | 30 pcs/tray | |
| Vacuum Bag | 5 tray per Vacuum bag (150pcs per bag) | |
| Outer Box | 4 bags = 600 pcs/carton | |
| # | Timer Dex | / } // |

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com REVISED: 08.03.2018

ABRACON IS ISO9001-2015 CERTIFIED