



## Mark I Safety Helmet

This lightweight helmet combines safety with economy and is designed for basic general use.

Please insert the following three digit number in place of the dashes into the code of your required Helmet to indicate your colour selection: 100 White, 200 Yellow, 300 Green, 500 Blue, 600 Red, 800 Orange

- Shell manufactured from UV stabilised high density Polyethylene
- Light and comfortable to wear
- Helmet offers 440v electrical insulation
- Integral rain channel for greater comfort in poor weather
- Slip ratchet adjustable headband
- Conforms to EN 397, ANSI Z89

Product	Code	Description
Mark I Safety Helmet	AHA010- 000- — — —	This lightweight helmet combines safety with economy and is designed for basic general use.



## Mark 2

A popular, tough and functional helmet. Helmet Shell manufactured from impact-resistant UV stabilised high density polyethylene.

Please insert the following three digit number in place of the dashes into the code of your required Helmet to indicate your colour selection: 100 White, 200 Yellow, 300 Green, 500 Blue, 600 Red, 800 Orange

- Adjustable 6-point low density polyethylene harness
- Fully adjustable slip ratchet headband
- Large area for printing logos
- Conforms to EN397, ANSI Z89
- Helmet offers 440v electrical insulation
- 530-620mm sizing (6 1/2" - 7 3/4")

Product Code	Description
Mark 2 AHB010-000-__ __	A popular, tough and functional helmet. Helmet Shell manufactured from impact-resistant UV stabilised high density polyethylene.



### **Mark 3 Comfort Plus**

Traditionally Europe's most popular design, these stylish helmets are tough, functional and offer an extremely comfortable secure fit on the head for prolonged periods of use. Designed for prolonged wearer comfort.

Please insert the following three digit number in place of the dashes into the code of your required Helmet to indicate your colour selection: 100 White, 200 Yellow, 300 Green, 500 Blue, 600 Red, 800 Orange

- Replaceable foam sweatband, 6-point terylene webbing comfort plus suspension harness
- Shell manufactured from impact-resistant UV stabilised high density polyethylene
- Wide area on the front of helmet for corporate logos or images
- Fully adjustable harness offers a secure safe fit of helmet
- Light well balanced design with low dome profile
- Helmet offers 440v electrical insulation
- Incorporates a rain channel
- Accepts Cliptite accessories
- Conforms to EN397, ANSI Z89
- 530-620mm sizing (6 1/2" - 7 3/4")

Product Code	Description
<a href="#">Mark III</a> AHC130-000-__ _	Wheel Ratchet Adjustment System
<a href="#">Mark III</a> AHC110-000-__ _	Slip Ratchet Adjustment System



## **FF European Safety Helmet**

A continental style flat-fronted helmet with closeable ventilation ports providing greater comfort in warmer weather.

Please insert the following three digit number in place of the dashes into the code of your required Helmet to indicate your colour selection: 100 White, 200 Yellow, 300 Green, 500 Blue, 600 Red, 800 Orange

- Shell manufactured from UV stabilised High Density Polyethylene
- Replaceable Nomaz fully absorbent Leatherette Sweatband
- Closeable ventilation ports
- 6-point Suspension harness
- Comfort Plus or Standard Poly harness
- Slip Ratchet Adjustable Headband
- Accepts Cliptite™ accessories
- Conforms to EN 397, ANSI Z89

Product	Code	Description
<a href="#">FF</a> <a href="#">European</a>	AHL110-000---	Comfort Plus/Slip.
<a href="#">FF</a> <a href="#">European</a>	AHL040-000---	Standard Poly/Slip & Sweatband.

### Mark VII R Features



### Mark VII R Options



## Mark 7R Safety Helmet

The Mark 7R safety helmet has been designed with comfort, performance and style in mind and incorporate the most innovative features seen yet on a safety helmet.

Please insert the following two digit number in place of the dashes into the code of your required Helmet to indicate your colour selection: 01 White, 02 Yellow, 03 Green, 05 Blue, 06 Red, 08 Orange

- Terylene webbing harness with fully absorbent leatherette comfort band
- Comes fitted with Sureslide® Retractaspec, is ventilated and with Easyjust® harness adjustment system
- Short peak option available
- Push and Twist Lok™ wheel ratchet option available
- Non-ventilated option available

Product	Code	Description
<a href="#"><u>Mark VII R1 Safety Helmet</u></a>	AHM120-10_-_00	Standard Peak, Non-Ventilated, EasyJust™ Slip Ratchet
<a href="#"><u>Mark VII R2 Safety Helmet</u></a>	AHM140-10_-_00	Standard Peak, Non-Ventilated, Push and Twist-Lok™ Wheel Ratchet
<a href="#"><u>Mark VII R3 Safety Helmet</u></a>	AHN120-10_-_00	Standard Peak, Ventilated, EasyJust™ Slip Ratchet
<a href="#"><u>Mark VII R4 Safety Helmet</u></a>	AHN140-10_-_00	Standard Peak, Ventilated, Push and Twist-Lok™ Wheel Ratchet
<a href="#"><u>Mark VII R5 Safety Helmet</u></a>	AHP120-10_-_00	Short Peak Surveyor, Non-Ventilated, EasyJust™ Slip Ratchet
<a href="#"><u>Mark VII R6 Safety Helmet</u></a>	AHP140-10_-_00	Short Peak Surveyor, Non-Ventilated, Push and Twist-Lok™ Wheel Ratchet
<a href="#"><u>Mark VII R7 Safety Helmet</u></a>	AHQ120-10_-_00	Short Peak Surveyor, Ventilated, EasyJust™ Slip Ratchet

[Mark VII R8](#)  
[Safety](#)  
[Helmet](#)

AHQ140-  
10\_-00

Short Peak Surveyor,  
Ventilated, Push and Twist-  
Lok™ Wheel Ratchet



## **Sweatband for Mark I/II/III and FF European Helmet**

Available in two styles: 250mm Nomaz Leatherette,  
Standard Nylon/foam

Product	Code	Description
<a href="#">Sweatband</a>	AHA800-000-000	250mm Nomaz Leatherette
<a href="#">Sweatband</a>	AHA820-000-000	Standard Nylon/foam