

CHART-TEMP® Temperature Recorders

CT-100 Series



Comes with
Extra Charts!



CT-300F-1H shown smaller than actual size.

**From -40 to 260°C
(-40 to 500°F)
Low-Temperature
Recorders with Ranges
Up to 104°C (220°F) and
Either 1- or 7-Day Charts
and 2% Accuracy
Oven Recorders with
Ranges Up to 260°C
(500°F) and Either
1- or 24-Hour Charts
with 3% Accuracy**

OMEGA® CHART-TEMP® recorders are dry-stylus, spring-wound, clock-driven circular chart recorders. Simply rewind the drive when replacing the chart. These recorders are excellent for recording temperatures inside buildings, refrigerators, or ovens. Units with ranges up to 260°C (500°F) are available.



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

Specifications

Dimensions: 82.5 H x 100 mm diameter
(3.26 x 3.94")

Weight:

High-Temp Models: 397 g (14 oz)
Low-Temp Models: 600 g (21 oz)

Low-Temperature Recorders

To Order		
Model No.	Temperature Range	Charts Model No.
CT-100AF-(*)	0 to 100°F	(*)-100F
CT-120AF-(*)	20 to 120°F	(*)-120F
CT-160AF-(*)	-40 to 160°F	(*)-160F
CT-220AF-(*)	20 to 220°F	(*)-220F
CT-70AF-(*)	-30 to 70°F	(*)-70F

* Insert "1" for 1-day or "7" for 7-day recorder. Units with "-7" suffix are 7-day recorders.

Ordering Examples: CT-100AF-1, 1 hr recorder with 0 to 100°F temperature range.

OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years.

High-Temperature Recorders

Model No.	Temperature Range	Charts Model No.
CT-300F-(*)	70 to 300°F	(*)-300F-CHART
CT-400F-1H	70 to 400°F	(*)-400F-CHART
CT-500F-(*)	70 to 500°F	(*)-500F-CHART
CT-150C-1H	20 to 150°F	1H-150C-CHART
CT-200C-1H	20 to 200°C	1H-200C-CHART
CT-260C-1H	20 to 260°C	1H-260C-CHART

* Insert "1H" for 1-hour or "24H" for 24-hour recorder. Units with "-1H" suffix are 1-hour recorders.

Ordering Example: CT-500F-1, 1-hour recorder with 70 to 500°F temperature range.

OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years.