


LJ6C Metal Face Plates

Our range of metal faceplates are ideal for installing into situations where matching the surrounding décor is important. This may mean that the Standard white ABS face plates are unsuitable. These faceplates have been designed specifically for the Enhanced Net 5 Compact LJ6C module, they fit perfectly onto flush wall mount back boxes.

The face plates are available in a wide selection of finishes and all come in single, dual and 4 way variations and are available from stock. The different finishes are; Georgian Rope Edge Brass, Victorian Polished Brass, Graphite, Brushed Steel, Mirror Chrome, Satin Chrome and Iridium Black.



Features / Benefits

- Available in a wide range of finishes •
- Designed to fit the Net 5 Enhanced LJ6C Module •
 - Available in 7 different finishes •
- Single and Dual gang faceplates are available •

SPECIFICATION

WIDTH	Single - 91mm	Double - 151mm
HEIGHT	Single - 91mm	Double - 91mm
DEPTH	Single - 9mm	Double - 9mm

FINISHES

Georgian Rope Edged Brass	Hand-polished pressed brass
Victorian Polished Brass	Hand-polished pressed brass
Mirror Chrome	Bright Nickel and Chromium hand-polished pressed Steel plate
Satin Chrome	Satin Chrome plated hand-polished pressed Steel Plate
Iridium Black	Black Chrome plate hand-polished pressed Steel Plate
Graphite	Grey painted finish on Zintec plate
Brushed Steel	Matt Chrome finish achieved using brushed Stainless Steel

ORDERING INFORMATION

Product Description

Georgian Rope Edge Brass one gang dual loaded faceplate
 Victorian Polished Brass one gang dual loaded faceplate
 Mirror Chrome one gang dual loaded faceplate
 Satin Chrome one gang dual loaded faceplate
 Iridium Black one gang dual loaded faceplate
 Graphite one gang dual loaded faceplate
 Brushed steel one gang dual loaded faceplate
 Georgian Rope Edge Brass two gang quad loaded faceplate
 Victorian Polished Brass two gang quad loaded faceplate
 Mirror Chrome two gang quad loaded faceplate
 Satin Chrome two gang quad loaded faceplate
 Iridium Black two gang quad loaded faceplate
 Graphite two gang quad loaded faceplate
 Brushed Steel two gang quad loaded faceplate

Part Number

008-001-014-00
 008-001-014-01
 008-001-014-02
 008-001-014-03
 008-001-014-04
 008-001-014-05
 008-001-014-06
 008-001-030-00
 008-001-030-01
 008-001-030-02
 008-001-030-03
 008-001-030-04
 008-001-030-05
 008-001-030-06