

Cat6 Patch Cables


Unbooted Cat6 UTP Patch Cables

Part No: 1996 - (Length) + (Colour) see chart

Manufactured using stranded Cat.6 stranded UTP cable, the assemblies feature high quality 50 micron gold RJ45 plugs and UL approved Cat.6 stranded cable.

Features & Benefits

- Manufactured using high quality 50 micron gold RJ45 plugs and UL approved Cat.6 stranded cable.
- Cable specification; 24 AWG ETL verified EIA/TIA-568A Cat.6 UTP with built-in centre spine which separates out each of the 4 twisted pairs.
- Designed to give quality assured, fault-free data/voice transmission within high speed Gigabit style networks.
- Fully backward compatible cables with both Cat.5 and Cat.5E networks & systems.
- Available in various colours and lengths.
- Cable labelling service available on short lead time, price quoted is per label, normally 2 labels required per cable one at each end.





Cat6 Patch Cables

Unbooted Cat6 UTP Patch Cables

Part No: 1996 - (Length) + (Colour) see chart

Part Number Chart

Length	Beige	Black	Blue	Green	Grey
0.3 Metre	1996-0.3	1996-0.3BK	1996-0.3B	1996-0.3G	1996-0.3GY
0.5 Metre	1996-0.5	1996-0.5BK	1996-0.5B	1996-0.5G	1996-0.5GY
1 Metre	1996-1	1996-1BK	1996-1B	1996-1G	1996-1GY
1.5 Metre	1996-1.5	1996-1.5BK	1996-1.5B	1996-1.5G	1996-1.5GY
2 Metre	1996-2	1996-2BK	1996-2B	1996-2G	1996-2GY
3 Metre	1996-3	1996-3BK	1996-3B	1996-3G	1996-3GY
5 Metre	1996-5	1996-5BK	1996-5B	1996-5G	1996-5GY
8 Metre	1996-8	1996-8BK	1996-8B	1996-8G	1996-8GY
10 Metre	1996-10	1996-10BK	1996-10B	1996-10G	1996-10GY
15 Metre	1996-15	1996-15BK	1996-15B	1996-15G	1996-15GY
30 Metre	1996-30	1996-30BK	1996-30B	1996-30G	1996-30GY



Cat6 Patch Cables

Unbooted Cat6 UTP Patch Cables

Part No: 1996 - (Length) + (Colour) see chart

Part Number Chart

Length	Orange	Pink	Purple	Red	White	Yellow
0.3 Metre	1996-0.3RG	1996-0.3PK	1996-0.3PR	1996-0.3R	1996-0.3W	1996-0.3Y
0.5 Metre	1996-0.5RG	1996-0.5PK	1996-0.5PR	1996-0.5R	1996-0.5W	1996-0.5Y
1 Metre	1996-1RG	1996-1PK	1996-1PR	1996-1R	1996-1W	1996-1Y
1.5 Metre	1996-1.5RG	1996-1.5PK	1996-1.5PR	1996-1.5R	1996-1.5W	1996-1.5Y
2 Metre	1996-2RG	1996-2PK	1996-2PR	1996-2R	1996-2W	1996-2Y
3 Metre	1996-3RG	1996-3PK	1996-3PR	1996-3R	1996-3W	1996-3Y
5 Metre	1996-5RG	1996-5PK	1996-5PR	1996-5R	1996-5W	1996-5Y
8 Metre	1996-8RG	1996-8PK	1996-8PR	1996-8R	1996-8W	1996-8Y
10 Metre	1996-10RG	1996-10PK	1996-10PR	1996-10R	1996-10W	1996-10Y
15 Metre	1996-15RG	1996-15PK	1996-15PR	1996-15R	1996-15W	1996-15Y
30 Metre	1996-30RG	1996-30PK	1996-30PR	1996-30R	1996-30W	1996-30Y