

CREALITY



Ender Precise Screwdriver Kit 22PCS

MFR: 4008060007

Product Information

Magnetic Inner Box

Screwdriver set head adsorption does not fall apart.

Easy to Access

CREALITY

The tool for Ender
Tasting tool

22 PCS

Precise screwdriver kit

40MM EXTENDED SCREWDRIVER SET HEAD EJECTION
OPEN CAP DESIGN



Exquisite craftsmanship | Humane design
Aesthetic appreciation

Handy, practical, ull of design
and more humanized home tools

Ender

A dark grey, rectangular power bank with the word "Ender" embossed on its surface. It is positioned on a dark desk next to a black keyboard and a smartphone. The background includes a white fan and a white mouse.

CREALITY

Fusion of modern aesthetic satisfy
the taste of life




Cover almost every scenario of daily household use



Ejection structure Magnetic suction inner box

Magnetic inner box, screwdriver set head adsorption does not fall apart, easy to access.






The ejection open
One click to start

Aluminum alloy cutter arbor

Hard anodized, the surface of the blade is more beautiful and exquisite.

Handle grip is comfortable and ergonomic design.






Handle cap Built-in bearing

Straight bearing inside the top cap, better concentricity. Rotate more smoothly, giving you a better disassembly experience.

Built-in strong magnet Easy pulling and inserting

Built-in strong magnetism, easy to pull and insert, magnetic transmission to the head, the head can easily suck up small screws.











Both hardness and torsion



Screwdriver set head comparison table

Applicable specifications Applicable scenes

 PH	PH000/PH00/PH0	Cellphone, Watch, Notebook,
	PH1/PH2	Common household screws, self-tapping screws
 SL	SL0.3	The precise watch instrument
	SL0.4/SL0.6	Common household screws, self-tapping screws
 HEX socket head	H1.5/H2.0/H3	Dismantling models, engines, firearms, knives, bicycles, motorcycles.
 SL	SL0.3	The precise watch instrument
	SL0.4/SL0.6	Common household screws, self-tapping screws
 Plum type	T1/T2	Huawei, OPPO and other cell phones dedicated.
	T3/T4/T5 T/6 TR8空心	Commercially sold cell phones, hard drives MACBOOK notebooks and other small electronic products.
 Five-star type	P2 P5	Apple cell phones and Apple peripheral products with
 Five-star type	Y0.6	
 Cross in the plate	CC2.2	

Product size





Product parameters

Let you better understand our products

Name: GT320

Brand: Ender

Color: Black/White

Box Material: ABS+PC

Cutter arbor material: Aluminum alloy

Cutter arbor size: 13*111

Screwdriver set head size: 4*40

Package size: 180*80*19.5

Screwdriver set head material: Imported S2 alloy steel

Screwdriver set head model

- | | | | | |
|--------------------------------|--------------------------------|--------------------------------|------------------------------|------------------------------|
| <input type="checkbox"/> PH000 | <input type="checkbox"/> PH00 | <input type="checkbox"/> PH0 | <input type="checkbox"/> PH1 | <input type="checkbox"/> PH2 |
| <input type="checkbox"/> SL1.5 | <input type="checkbox"/> SL3.0 | <input type="checkbox"/> SL3.5 | <input type="checkbox"/> T1 | <input type="checkbox"/> T2 |
| <input type="checkbox"/> T3 | <input type="checkbox"/> T4 | <input type="checkbox"/> T5 | <input type="checkbox"/> T6 | <input type="checkbox"/> TR8 |
| <input type="checkbox"/> H1.5 | <input type="checkbox"/> H2.0 | <input type="checkbox"/> H3.0 | <input type="checkbox"/> P2 | <input type="checkbox"/> P5 |
| <input type="checkbox"/> CC2.2 | <input type="checkbox"/> Y0.6 | | | |

PRODUCT DISPLAY

