

3DPrintMill (CR-30) Basic Maintenance Kit

MFR: 4006010002

Item Name	Spec	QTY	Unit
Hexagon socket countersunk head screws	M3*8, 40CR, Black, ROHS	1.00	PCS
Hexagon socket countersunk head screws	M4*16, SUS304, ROHS	1.00	PCS
Hexagon socket countersunk head screws	M3*18, SUS304, ROHS	2.00	PCS
Hexagon socket countersunk head screws	M4*18, 40CR, Black, ROHS	3.00	PCS
Hexagon socket countersunk head screws	M3*10, SUS304, ROHS	1.00	PCS
Hexagon socket flat head screws	M3*12, SUS304, ROHS	2.00	PCS
Hexagon socket flat head screws	M4*18, SUS304, ROHS	1.00	PCS
Hexagon socket flat head screws	M3*8, SUS304, ROHS	2.00	PCS
Hexagon socket flat head screws	M5*18, SUS304, ROHS	3.00	PCS
Hexagon socket flat head screws	M3*22, SUS304, ROHS	1.00	PCS
Hexagon socket flat head screws	M3*14, SUS304, ROHS	1.00	PCS
Hexagon socket flat head screws	M5*40, SUS304, ROHS	2.00	PCS
Hexagon socket flat head screws	M5*30, SUS304, ROHS	2.00	PCS
Hexagon socket flat head screws	M5*12, SUS304, ROHS	2.00	PCS
Hexagon socket flat head screws	M5*10, SUS304, ROHS	2.00	PCS
Hexagon socket flat head screws	M5*8, SUS304, ROHS	3.00	PCS
Hexagon socket flat head screws	M4*20, SUS304, ROHS	2.00	PCS
Hexagon socket flat head screws	M4*16, SUS304, ROHS	2.00	PCS
Hexagon socket flat head screws	M4*12, SUS304, ROHS	2.00	PCS
Hexagon socket flat head screws	M4*8, SUS304, ROHS	2.00	PCS
Hexagon socket flat head screws	M4*8, SUS304, ROHS	2.00	PCS
Hexagon socket flat head screws	M3*18, SUS304, ROHS	2.00	PCS
Hexagon socket flat head screws	M3*16, SUS304, ROHS	2.00	PCS
Hexagon socket flat head screws	M3*10, SUS304, ROHS	2.00	PCS
Hexagon socket flat head screws	M3*4, SUS304, ROHS	2.00	PCS
Hexagon socket head screw	M3*12, SUS304, ROHS	4.00	PCS
Hexagon socket head screw	M4*25, SUS304, ROHS	1.00	PCS
Hexagon socket head screw	M3*20, SUS304, ROHS	1.00	PCS
Hexagon socket head screw	M4*20, SUS304, ROHS	4.00	PCS
Hexagon socket head screw	M5*25, 40CR, Black, ROHS	2.00	PCS
Hexagon socket head screw	M4*16, SUS304, ROHS	2.00	PCS
Hexagon socket head screw	M3*25, SUS304, ROHS	1.00	PCS
Hexagon socket head screw	M3*18, SUS304, ROHS	2.00	PCS
Hexagon socket head screw	M2*10, 40CR, Black, ROHS	2.00	PCS
Hexagon socket head screw	M2*6, 40CR, Black, ROHS	4.00	PCS
Hexagon socket head spring washer combination screw	M5*45, 40CR, Black ROHS	4.00	PCS
Hexagon socket head spring washer combination screw	M5*20, 40CR, Black ROHS	1.00	PCS
Hexagon socket head spring washer combination screw	M5*30, 40CR, Black ROHS	2.00	PCS
Hexagon socket head spring washer combination screw	M5*25, 40CR, Black ROHS	4.00	PCS
Cross recessed round head with screw	M3*4, SUS304, ROHS	1.00	PCS
Hexagon socket head screw	M3*20, Black, ROHS	1.00	PCS
Hexagon socket set screw with flat end (top wire)	M3*2, 40CR, Black, ROHS	1.00	PCS

Hexagon socket set screw with flat end (top wire)	M3*3, 40CR, Black, ROHS	4.00	PCS
Φ5.5 Clip	PA66, Blue plastic opening clamp	3.00	PCS
Black, nylon cable tie	4*150mm, Black	100.00	PCS
Red silicone wire	3135/#16, L90mm	1.00	PCS
Hexagon socket countersunk head screws	M4*20, 40CR, Black, ROHS	2.00	PCS
Hexagon socket head screw	M2*12, SUS304, ROHS	4.00	PCS
Hexagon socket flat head screws	M4*4, SUS304, ROHS	2.00	PCS
Hexagon socket head spring washer combination screw	M4*20, 40CR, Black	4.00	PCS
Hexagon socket head spring washer combination screw	M5*12, 40CR, Black	4.00	PCS
Hexagon socket countersunk head screws	M4*50, SUS304, ROHS	1.00	PCS
Hexagon socket countersunk head screws	M4*55, SUS304, ROHS	1.00	PCS
Motor limit wire	Y axis limit wire, L600mm	1.00	PCS
Motor wire	E axis motor wire, L800mm	1.00	PCS
Display wire	FC display wire, L500mm	1.00	PCS
Power supply wires (Red & Black,)	Power silicone cable, L540mm	1.00	PCS
Power supply wires (Red & Black,)	Motherboard power silicone cable, L250mm	1.00	PCS
Motor wire	Z axis motor wire, L700mm	1.00	PCS
Motor wire	Y axis motor wire, L850mm	1.00	PCS
Motor wire	X axis motor wire, L1250mm	1.00	PCS
Power supply wire	Socket ground wire, L100mm, ROHS	1.00	PCS
Power ground wire	Power ground wire, L70mm, ROHS	1.00	PCS
Power supply wires	Nozzle ground wire, L1500mm, ROHS	1.00	PCS
Aviation header cable	Hot bed transfer wire, L300mm, ROHS	1.00	PCS
Aviation header cable	Hot bed wire, L350mm, ROHS	1.00	PCS
Motor limit wire	Y axis limit wire, L600mm, ROHS	1.00	PCS
Power supply wire	Screen ground wire, L390mm, ROHS	1.00	PCS
Hexagon socket flat head screws	M4*40, SUS304, ROHS	1.00	PCS
Optocoupler switch with wire	Optocoupler switch, 150mm, ROHS	2.00	PCS
Photoelectric switch	Photoelectric switch, ROHS	2.00	PCS
Filament Sensor wire	Filament Sensor wire, L900mm	1.00	PCS