
Mounting carrier with strain relief; 5-way; for inline splicing connector with lever; for screw mounting; gray



www.wago.com/221-2505






 $\label{thm:condition} \textbf{Subject to changes. Please also observe the further product documentation!}$

www.wago.com/221-2505





Data

Physical data

Width	47.8 mm / 1.882 inch
Height from the surface	6.5 mm / 0.256 inch
Depth	100 mm / 3.937 inch

Material data

Note on material data	Information on material data can be found here	
Color	gray	
Weight	9.6 g	

Commercial data

PU (SPU)	25 (5) Pieces
Packaging type	box
Country of origin	CN
GTIN	4055144066548
Customs tariff number	39269097900

Subject to changes. Please also observe the further product documentation!

WAGO Private Limited
NH No. 8, Block No. 94 Vadsala,
Block No. 1187 Varnama, Village Varnama / Vadsala
Ta. & Distt. Vadodara, Vadodara, Gujarat-391243
Phone: +91-265-6812100 | Email: info.india@wago.com

Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/221-2505



Optional accessories

Marking	accesso	ries

Marking strip



Item no.: 210-334

Marking strips; as a DIN A4 sheet; Strip width 5 mm; Strip length 182 mm; plain; Self-adhesive; white

www.wago.com/210-334

Mounting

Mounting accessories



Item no.: 209-119

Fixing screw; for 209-120 mounting carrier

www.wago.com/209-119



Item no.: 209-123

Mounting foot with screw; can be screwed on terminal blocks with fixing flange; 6.4 mm wide; gray

www.wago.com/209-123



Item no.: 209-120

Mounting foot; can be snapped on terminal blocks with snap-in mounting foot; for mounting on relay-modules; 6.4 mm wide; gray

www.wago.com/209-120

Downloads

Documentation

Additional Information

Technical Section

pdf

Download

Technical explanations

2.2 MB

CAD/CAE-Data

CAE data

ZUKEN Portal 221-2505

URL

Download

CAD data

2D/3D Models 221-2505

URL

Download

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 221-2505

URL

Download

Subject to changes. Please also observe the further product documentation!

WAGO Private Limited

NH No. 8, Block No. 94 Vadsala,

Block No. 1187 Varnama, Village Varnama / Vadsala

Ta. & Distt. Vadodara, Vadodara, Gujarat-391243

Phone: +91-265-6812100 | Email: info.india@wago.com

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/221-2505



Mounting carrier with strain relief; 5-way; for inline splicing connector with lever; for screw mounting; gray

Installation Notes

Installation



Place the inline splicing connector on the carrier in front of the mounting position.



Push the connector to the center position until it snaps into place.



Mounting carrier without strain relief – snapped onto DIN-rail




Various combinations of 1- to 5-connector mounting carriers are possible via side-by-side latching mechanism.

Strain relief

 $\label{thm:condition} \textbf{Subject to changes. Please also observe the further product documentation!}$

www.wago.com/221-2505





3-pole mounting carrier with strain relief

 $\label{lem:condition} \textbf{Subject to changes. Please also observe the further product documentation!}$

WAGO Private Limited
NH No. 8, Block No. 94 Vadsala,
Block No. 1187 Varnama, Village Varnama / Vadsala
Ta. & Distt. Vadodara, Vadodara, Gujarat-391243
Phone: +91-265-6812100 | Email: info.india@wago.com

Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.