

# INTERCHANGEABLE WALL PLUG POWER SUPPLY 9VDC 15WATT

## POWERPAX: SW4463-B



### Features:

- Interchangeable AC Heads
- 1 Year Warranty
- Level VI Efficiency
- Worldwide Approvals

### Description:

Our range of 15 Watt Interchangeable wall plug power supplies provide 15 Watts of continuous power with the flexibility of worldwide usage as they are supplied with UK, Euro, USA & Auz AC Heads , all Efficiency Level VI and carry worldwide safety approvals.

Specification	
Part Code	SW4463-B
Input Voltage Range	90-264 Vac
Input Frequency Range	50/60Hz +/- 3Hz
Input Current Rated	0.5A Max
Input AC Heads	UK, Euro, USA & Auz
Output Voltage Rating	+9V
Output Current Range	1.67A
Output Min Current	0.0A
Output Connection Type	2.1x5.5x12mm centre positive – Straight angle
Line and Load Regulation	+/- 5%
Ripple & Noise	150mVp-p
Efficiency	84.14%Min
Short-Circuit Protection	No Damage
Over Current Protection	The output shall be protected against the over current conditions.
Operating Temperature	0°C to +40°C
Storage Temperature	-20°C to +80°C
Operating Humidity	10% to 90%
Storage Humidity	10% to 90%
Hi-Pot	3000VAC 5mA 1min
Leakage Current	0.25mA max
Safety Standard	UL, CSA, GS, CE, UK, SAA
EMI Standard	FCC part 15: Class B EN55022:2010, Class B EN 55024:2010 EN 61000-4-2 EN 61000-4-3 EN 61000-4-4 EN 61000-4-5
MTBF	50K Hours
Size mm max.	85.5 (L) x 39.78 (W) x 43.8 (H)
Weight	112 g

### General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.


### POWERPAX

TT Electronics IoT Solutions Ltd  
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK  
t: +44 (0) 1429 852 500

# INTERCHANGEABLE WALL PLUG POWER SUPPLY 9VDC 15WATT

## POWERPAX: SW4463-B

### Diagrams



#### General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

### POWERPAX

TT Electronics IoT Solutions Ltd  
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK  
t: +44 (0) 1429 852 500