

10m USB 3.0 Active Extension Cable - M/F

Product ID: USB3AAEXT10M



The USB3AAEXT10M, 10-meter Active USB 3.0 Extension Cable, offers one USB type-A (male) connector and one USB type-A (female) connector, and provides an active extension of USB 3.0 devices of up to 10-meters (32.8-feet).

An all-in-one cable for overcoming distance restrictions as well as power source limitations; the active USB 3.0 extension cable incorporates bus-powered active circuitry to ensure performance beyond the length limits of standard USB cables. Up to 2 of these cables can be daisy-chained together, allowing the connection to be extended a total of 20-meters. If necessary, the USB device can be powered from a wall outlet using the Universal AC power adapter provided with the cable.

The USB3AAEXT10M extension cable (USB Extender) supports high speed USB 3.0 transfer rates of up to 5Gbps, and is backed by StarTech.com's 2-year Warranty.

Certifications, Reports and Compatibility

Applications

- Extend the distance of USB peripherals beyond the USB 3.0 3-meter limitation
- Cascade up to 2 levels
- Backwards compatible with USB 2.0/1.1 devices

Features

- Fully shielded for error-free connections
- Plug-and-play, no driver required

- USB bus-powered
- Universal external power source also included
- Blue LED indicator x1 for Extension Cable and USB port connection status monitoring
- Compatible with PC Windows 8/7/Vista/XP and Mac computer systems

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride

Connector(s)

Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
Connector B	USB Type-A (9 pin) USB 3.0 (5 Gbps)

Special Notes / Requirements

Note	Cascade up to 2 USB3AAEXT10M devices together for further extension
------	---

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.35 A
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	H
Power Consumption (In Watts)	10

Physical Characteristics

Color	Black
-------	-------



Cable Length	32.8 ft [10 m]
Product Length	32.8 ft [10.0 m]
Product Width	0.8 in [20.0 mm]
Product Height	0.4 in [10.0 mm]
Weight of Product	17.3 oz [491.0 g]

Packaging Information

Package Quantity	1
Package Length	8.4 in [21.4 cm]
Package Width	8.9 in [22.5 cm]
Package Height	2.4 in [60.0 mm]
Shipping (Package) Weight	26.8 oz [758.0 g]

What's in the Box

Included in Package	10 m USB 3.0 Active Extension Cable - M/F
	Universal Power Adapter
	Plug Adapters for North America, UK, Europe, and Australia

****Product appearance and specifications are subject to change without notice.***

