

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2167950001](#)
Status: **Active**
Overview: [Sentrality Pin and Socket Interconnect System](#)
Description: Sentrality 11.0mm Top-entry, Eye-of-Needle Press-fit Socket Assembly with +/- 1.00mm Self-alignment Capability in Tray

Documents:

Drawing (PDF)	Test Summary 2043131234-TS-000 (PDF)
Product Specification 2151130000-PS-000 (PDF)	Datasheet (PDF)
Application Specification 2151130000-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification 2167950000-PK-000 (PDF)	

General

Product Family	PCB Receptacles
Series	216795
Application	Board-to-Board, Busbar-to-Board, Power
Comments	Current and voltage performances are dependent upon application variables.
Overview	Sentrality Pin and Socket Interconnect System
Product Name	Sentrality
UPC	195842227903

Physical

Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	11.00mm
Durability (mating cycles max)	200
Glow-Wire Capable	No
Guide to Mating Part	Yes
Height Above Board	11.84mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Mating Orientation	Top-entry
Net Weight	19.746/g
Number of Rows	1
Orientation	Vertical
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	N/A
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Through Hole - Compliant Pin


Electrical

Current - Maximum per Contact	300.0A
Voltage - Maximum	600V

Material Info

Reference - Drawing Numbers

Application Specification	2151130000-AS-000
Packaging Specification	2167950000-PK-000
Product Specification	2151130000-PS-000
Sales Drawing	2167950000-SD-000
Test Summary	2043131234-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contained Per -
D(2021)10043-DC (17
Jan 2022)
4,4'-(1-
Methylpropylidene)bisphenol
Medium-chain
chlorinated paraffins
(MCCP)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[216795](#) Series

Mates With

11.0mm Male Pin [213902](#)

This document was generated on 03/18/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION