



3G/4G/WiFi Ceiling mounted, weather resistant, 2 port MiMo diversity Antenna

Key Features

- Heavy duty screw mount
- Dual port MiMo
- Designed for public transport



General Description

The Tango421 antenna is good for vehicles and provides access to 3G and 4G cellular networks.

The Tango 421 can be used with one half of the antenna accessing the mobile networks and the second antenna providing a WiFi or Bluetooth service within the vehicle to its occupants.

The Tango 421 is a robustly built ceiling antenna that is weather and UV resistant for deploying on the roof of the intended vehicle. The antenna has a zinc plated steel backing plate with Stainless 12mm metal securing stud for mounting onto the vehicle.

Supplied as standard with SMA male connectors and 1.5m of cable. Alternative connectors and cable lengths may be specified for volume orders.

Additional Considerations

- Horizontal and vertical plane dual antenna
- PRO100 low loss cables
- ABS plastic radome



sales

email

web

fax

Registered in England No. 08405712 VAT Registration No. GB163 04 0349 Siretta Ltd Basingstoke Road Spencers Wood Reading Berkshire RG7 1PW






3G/4G/WiFi Ceiling mounted, weather resistant, 2 port MiMo diversity Antenna

Electrical Specifications

Impedance:	50 Ohm
VSWR:	≤2.5
Gain Port1 (Vertical)-M	1710 - 2170MHz: 2.5dBi 2300 - 2700MHz: 3dBi
Gain Port2 (Horizontal)-D	1710 - 2170MHz: 4dBi 2300 - 2700MHz: 6dBi
Frequency range:	1710 - 2170 / 2300 - 2700MHz
Beam Width:	H: 360° / 68°, E: 60° / 90°
Max Power:	10W
Isolation:	<-20dB
Polarization:	Vertical

Mechanical Specifications

Operating Temperature:	-30 - +60°C
Dimensions:	Ø 90 x H40.5mm
Cable:	Low Loss PRO100 1.5M x 2
Connector:	SMA Male x 2
Material-radome:	ABS



sales +44(0)118 976 9014 +44(0)118 976 9020 email sales@siretta.com www.siretta.com

fax


web





3G/4G/WiFi Ceiling mounted, weather resistant, 2 port MiMo diversity Antenna

VSWR Antenna 1 - Vertical



VSWR Antenna 2 - Horizontal



Registered in England No. 08405712 VAT Registration No. GB163 04 0349 Siretta Ltd Basingstoke Road Spencers Wood Reading Berkshire RG7 1PW +44(0)118 976 9014 +44(0)118 976 9020 sales@siretta.com www.siretta.com

sales

email

web


fax






3G/4G/WiFi Ceiling mounted, weather resistant, 2 port MiMo diversity Antenna

Return Loss Antenna 1 - Vertical



Return Loss Antenna 2 - Horizontal



Registered in England No. 08405712 VAT Registration No. GB163 04 0349 Siretta Ltd Basingstoke Road Spencers Wood Reading Berkshire RG7 1PW +44(0)118 976 9014 +44(0)118 976 9020 sales@siretta.com www.siretta.com

sales

email

web


fax






3G/4G/WiFi Ceiling mounted, weather resistant, 2 port MiMo diversity Antenna

Isolation



Radiation Patterns

1710 - 2170MHz Antenna 1 - Vertical Port



Registered in England No. 08405712 VAT Registration No. GB163 04 0349 Siretta Ltd Basingstoke Road Spencers Wood Reading Berkshire RG7 1PW sales

email


web

fax






3G/4G/WiFi Ceiling mounted, weather resistant, 2 port MiMo diversity Antenna



1710 - 2170MHz Antenna 2 - Horizontal Port

2300 - 2700Hz Antenna 1 - Vertical Port



sales

email


web

fax





3G/4G/WiFi Ceiling mounted, weather resistant, 2 port MiMo diversity Antenna



2300 - 2700Hz Antenna 2 - Horizontal Port

Ordering Details

Part Number

Description

TANGO421/1.5M/SMAM/SMAM/S/S/29

3G/4G/WiFi Ceiling mounted, weather and UV resistant, 2 port MiMo diversity Antenna

Siretta Ltd Basingstoke Road Spencers Wood Reading Berkshire RG7 1PW

sales

email

web

fax