

ROCKER SWITCHES

PRODUCT NUMBER 1802.6123



TECHNICAL DATA

Product number	1802.6123	
Business unit	Switches, Sensors & Controls	
Product Manager	-	
Product family	Rocker switches	
Actuation type	direct	
Packing unit	500	
Weight	5.403 g	
Switch on continuous current (capacitive)	5 A	
Inrush current (capacitive)	70 A	
ROHS conform	yes	
Output	catalog before 2009 / Web-Shop / catalog	
Switching function	ON / OFF switch (DPST)	
Material fixed contact	Ag	
Number of poles	2 - pole	
connections	Solder terminal	
Mechanical life endurance	10E4	
Rating IEC	12 (4) A 250 V AC 1E4 8 (8) A 250 V AC 5E4	
Rating North America	15 A 125 V AC 3/4 HP 15 A 250 V AC 1 1/2 HP	
Contact resistance (new condition)	< 100 (1 A 12 V DC) mOhm	
Insulation resistance (new condition)	> 100 (500 V DC) MOhm	
Voltage strength at 250 V	➔ function insulation / basic insulation ➔ reinforced insulation ➔ small contact distance	1 500 V 3 000 V 500 V
Proof tracking	250 PTI	
Insulation spacing	acc. to EN 61058 for reinforced or double insulation	
Protection type	➔ Connection	IP 40 IP 40

	→ Actuator
Ambient temperature	→ connection side -20 °C ... +100 °C
Ambient temperature	→ Actuation side min. -20 °C ... +55 °C
Storage temperature	-40 °C ... +80 °C
Flammability	UL 94 V-2
Glow wire test temperature	850 °C
Actuators and additional actuators	rocker: PA, black, identification white
Housing description	housing: PA, black
Connection surface	→ bearing connection silver plated → external connection silver plated
Contact material	Ag
Contact distance	≥ 3 mm
Rating Code UL	R 149
Contact type	lifting contact
Plug force of the terminals	≤ 80 N
Approval marks	CSA / ENEC 05 / UL
Suitable for appliances of protection class	II
Additional labeling packing	0041.1644
Type of fastening	Snap fastening
Degree of pollution	3
Stock version	●

Technical changes reserved. Dimensions are not binding.

Detailed specifications available on request.

Marquardt GmbH · Schloss-Straße 16 · 78604 Rietheim-Weilheim · Germany
 Phone: +49 (0) 7424 / 99-0 · Fax: +49 (0) 7424 / 99-2399 · www.marquardt.com · marquardt@marquardt.de