

EXTERNAL DESKTOP POWER SUPPLY 48VDC 65WATT

POWERPAX: SW4328-C



Features:

- Universal Input
- IEC-320-C14 Input Connector
- 3 Year Warranty
- Efficiency Level VI
- Safety approved to: UL,CUL,FCC,GS,CE,RCM

Description:

Our Range of 65 Watt AC/DC switch mode power supplies provide 65 Watts of continuous output power in a high quality compact enclosure suitable for many general power applications.

Specification	
Part Number	SW4328-C
Input Voltage Range	100 → 240 Vac
Input Frequency Range	50 → 60Hz
Input Connector	IEC 320-C14
Input Current Rated	1.4A Max
Inrush Current	80 A Max. / 240 Vac (Cold start at 25°C, full load)
Leakage Current	<3.5mA
Efficiency	88%
Input Power(Output: No Load)	0.21 W (At 230Vac & No load)
Output Voltage Rating	48Vdc
Output Current Range	1.36A Max
Output Min Current	0A
Output Connection Type	2.1 x 5.5 x 12 mm centre positive – Straight
Line and Load Regulation	+/-5%
Over Voltage Protection	V out * 150% Max.
Over Load Protection	I out *180% Max.
Short Circuit Protection	Automatic recovery after short-circuit fault being removed
Ripple Voltage	480mV Max.
Hi-Pot	3000Vac 10mA 1min.
Safety Approved	UL,CUL,GS,PSE,BSMI,CB/RCM
EMI Standard	CE / FCC Class B
Operating Temperature Range	0°C → +40°C
Storage Temperature	-20°C → +80°C
Operating Humidity	20% to 80%
Storage Humidity	10% to 90%
Dimensions	115(L) x 53(W) x 38(H) mm
Product Weight	310g
Regulator Type	Switched Mode Power Supply

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.


POWERPAX

TT Electronics IoT Solutions Ltd
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK
t: +44 (0) 1429 852 500

EXTERNAL DESKTOP POWER SUPPLY 48VDC 65WATT

POWERPAX: SW4328-C

Diagrams



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

POWERPAX

TT Electronics IoT Solutions Ltd
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK
t: +44 (0) 1429 852 500